

13 12 11 10 9 8 7 6 5 4 3 2 1

MATERIALS AND FINISHES

BODY ZINC ALLOY
PLATED NICKEL

HOUSING PLOYESTER BUTYLENE TEREPHTALATE
COLOR: BLACK

CENTER CONTACT PHOSPHOR BRONZE
PLATED GOLD

INSULATOR POLYPROPYLENE (94-V2)

MOUNTING POST BRASS
PLATED TIN

SOLDER TAIL BRASS WIRE
PLATED TIN

LOCKWASHER PHOSPHOR BRONZE
PLATED NICKEL

JAM NUT BRASS
PLATED NICKEL


BNC JACK
INTERFACE

MXT


1/2-28 UNEF-2A

JAM NUT



LOCKWASHER



RECOMMENDED MOUNTING HOLE
PANEL THICKNESS: 5.50(.217) MAX
RECOMMENDED MOUNTING TORQUE:
0.56 N(5 INCH-LBS) MAX



RECOMMENDED PCB
CONFIGURATION



ES-73599-0000	INTERFACE
PS-73598-0051	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

73171-2980	73100-0067, ONE PER BAG
73100-0067	PLASTIC TRAYS
PART NO.	PACKAGING

CHG: REDREW IN SD
ADDED P/N
73171-2980
EC NO: URF2007-0396
DRAWN: TELAHARTY 2007/05/01
CHKD: SHAH 2007/05/01
APPR: JIM ENER 2007/05/01
A1

QUALITY
SYMBOLS
=0
=0

GENERAL TOLERANCES (UNLESS SPECIFIED)	
mm	INCH
4 PLACES ±	±
3 PLACES ±	±
2 PLACES ±	±
1 PLACE ±	±
ANGULAR ± 2 °	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM/IN	
DRAWN BY	DATE
C.M.HUNG	1993/02/01
CHECKED BY	DATE
APPROVED BY	DATE
KWH	1993/04/01
MATERIAL NO.	DOCUMENT NO.
SEE TABLE	SD-73100-0067

SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
METRIC		
BNC JACK, R/A, PCB RECEPTACLE, 75 OHMS BNC-J/RA/PCB		
MOLEX INCORPORATED		
SHEET NO. 1 OF 1		