

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IR	-		U	ECR-05-012760	1-OCT-05	-	JB
			V	ECR-10-020218	28DEC2010	PS	RRP
			W	ECO-13-015831	9OCT2013	CW	SH
			-	-	-	-	-

D

D

C


C

B

B


A

A









NOTES:

- 1 TOLERANCE UNLESS OTHERWISE SPECIFIED: 0,15.
- 2 BULK PACKAGING: TRUE POSITIONING OF THE SOLDER TINES IS NOT GUARANTEED.
- 3 SUPERSEDED BY 1-215876-3



1,27 TYP.

3,81



PRINTED CIRCUIT BOARD LAYOUT

(VIEW SHOWN IS CIRCUIT (NON-COMPONENT) SIDE OF BOARD.)

PRINTED CIRCUIT BOARD THICKNESS: 1,6mm NOMINAL.

TOLERANCE UNLESS OTHERWISE SPECIFIED:±0,05.

OVERALL: Ni 1.27µm MIN. ALL OVER THE CONTACTS SOLDER ZONE: Sn 2.5µm MIN. ON THE SOLDER ZONE OF THE CONTACT MATING ZONE: PLATING CONFIRMS TO PRODUCT REQUIREMENTS AS PER SPECIFICATION 108-19064	HOUSING, COLOR BLACK: PBT 20% GF, UL 94V-0 CONTACT INSERT: PBT, UL 94V-0 CONTACTS: PH, BRONZE	290 PCS IN A TRAY	1-215875-3
		50 PCS IN A TUBE (SEE SHEET 2)	3-215875-3
		BULK PACKAGED IN A BOX	2-215875-1
		126 PIECES IN MULTI-TUBE	1-215875-1
		TAPE MOUNTED 1000pcs./reel	215875-1
FINISH	MATERIAL	PACKAGING	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.v.EIJK	TE Connectivity		
		CHK M.v.ESSSEN			
		APVD R.SMEETS	NAME MODULAR JACK SIDE ENTRY 4/4 FOR PRINTED CIRCUIT BOARD		
		PRODUCT SPEC 108-19064			
		APPLICATION SPEC 114-19019	SIZE A2		
		WEIGHT -			
		CUSTOMER DRAWING	C-215875		
		SCALE 4:1	SHEET 1 OF 2		
			REV W		

NOTES:

5 TUBE IS TRANSPARANT PVC.

6 TUBE IS CLOSED AT BOTH ENDS BY A TAPE.

