

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

LOC

DIST

REVISIONS

© COPYRIGHT - By TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

AF

50

P

LTR

DESCRIPTION

DATE

DWN

APVD


B

REVISE PER ECR-13-013738

15FEB2014

GRZ

JL






1 CONTINUOUS STRIP ON REELS


2 WIRE SIZE IS 1000-2700 CMA ( 2 WIRES )  
(0.6+0.6mm) to (1.0+0.85mm) DIA  
CRIMP WIDTH IS 2.29 [.090], F TYPE3 INSULATION RANGE 2.54-3.05 [.100-.120] DIA  
CRIMP WIDTH IS 3.56 [.140], OVERLAP TYPE

4 0.002032 [.00080] MIN TIN PLATE

5 MATING TAB THK IS 0.81±0.025 [.032±.001].



SECTION A-A



SECTION B-B

1742882-1

PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN jr\_ruth 08DEC10

CHK PETE DESANTIS 08DEC10


APVD PETE DESANTIS 08DEC10

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:  
MM [ INCHES ]MATERIAL  
BRASSTOLERANCES UNLESS  
OTHERWISE SPECIFIED:0 PLC ± -  
1 PLC ± -  
2 PLC ± 0.25 [.010]  
3 PLC ± -  
4 PLC ± -  
ANGLES ± 5°  
FINISH

-4

STE

TE Connectivity

NAME

RECEPTACLE, FASTON, FLAG,  
AMPLIVAR, 6.35 [.250] SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1742882

SCALE 5:1

SHEET 1 OF 1

REV B