




2106391-1 SHOWN

RECEPTACLE ASSEMBLY

CONTACT

WIRE 3

DOM A±3.0

12.7012.7±0.8
STRIP AND RETAIN

2106391-2 SHOWN

RECEPTACLE ASSEMBLY

CONTACT

WIRE 3

DIM A±3.0

12.7±0.8
STRIP AND RETAIN

WIRE COLOR CHART

4	-	-	-	BLUE	-	-	BLUE	-	-	BLUE	-	-	BLUE	-	-	BLUE	-	-	BLUE	-	-	BLUE	-	-	BLUE	-	-	-
3	-	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE	-	WHITE	WHITE
2	-	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED	RED
1	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK	BLACK
POS	-1	-2	-3	-4	-5	-6	-7	-8	-9	-10	-11	-12	-13	-14	-15	-16	-17	-18	-19	-20	-21	-22	-23	-24	-25	-26	-27	-28

1 MATERIALS AND FINISH:
-CONTACTS: COPPER ALLOY
FINISH: TIN IN CONTACT AREA OVER NICKEL UNDERPLATE
-WIRE: 18 AWG, STRANDED, UL 1007 STYLE

2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (ROHS)

3 REFERENCE CHART FOR SPECIFIC WIRE COLOR/POSITION

2000.0

20 AWG

2

2-2106391-8

5000.0

18 AWG

2

2-2106391-7

381.0

18 AWG

2

2-2106391-6

304.8

24 AWG

4

2-2106391-5

304.8

24 AWG

3

2-2106391-4

304.8

24 AWG

2

2-2106391-3

101.6

24 AWG

4

2-2106391-2

101.6

24 AWG

3

2-2106391-1

101.6

24 AWG

2

2-2106391-0

304.8

22 AWG

4

1-2106391-9

304.8

22 AWG

3

1-2106391-8

304.8

22 AWG

2

1-2106391-7

101.6

22 AWG

4

1-2106391-6

101.6

22 AWG

3

1-2106391-5

101.6

22 AWG

2

1-2106391-4

304.8

20 AWG

4

1-2106391-3

304.8

20 AWG

3

1-2106391-2

304.8

20 AWG

2

1-2106391-1

101.6

20 AWG

4

1-2106391-0

101.6

20 AWG

3

2106391-9

101.6

20 AWG

2

2106391-8

304.8

18 AWG

4

2106391-7

304.8

18 AWG

3

2106391-6

304.8

18 AWG

2

2106391-5

101.6

18 AWG

4

2106391-4

101.6

18 AWG

3

2106391-3

101.6

18 AWG

2

2106391-2

101.6

18 AWG

1

2106391-1

DIM A

WIRE SIZE

POSN

PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.2
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-
FINISH

MATERIAL

-

DWN R BROWN 20APR2009

CHK M MOSTOLLER 20APR2009

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Customer Drawing

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A200779

C-2106391

-

SCALE 4:1

SHEET 1 OF 3

REV G

TE Connectivity

CABLE ASSEMBLY, RECEPTACLE, SLIMSEAL SSL CONNECTOR

1471-9 (3/11)

D

C

B

A

D


C

B


A

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
© COPYRIGHT 20	BY -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-		-	SEE SHEET 1	-	-	-



2106391-3 SHOWN
(SAME AS 2106391-2
EXCEPT 3 POSITION)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R BROWN	20APR2009	 TE Connectivity					
		CHK M MOSTOLLER	20APR2009						
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME CABLE ASSEMBLY, RECEPTACLE, SLIMSEAL SSL CONNECTOR					
		0 PLC ±-							
		1 PLC ±0.2							
		2 PLC ±-							
		3 PLC ±-							
		4 PLC ±-							
ANGLES ±-									
MATERIAL		FINISH					SIZE A200779		
-		-							
				RESTRICTED TO -					
							Customer Drawing		
				SCALE 4:1					
							SHEET 2		
				OF 3					
							REV G		

D

D

C



C

B

B

A

A



2106391-4 SHOWN
(SAME AS 2106391-2
EXCEPT 4 POSITION)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
R BROWN
CHK
M MOSTOLLER

20APR2009
20APR2009

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

Customer Drawing

TE Connectivity

CABLE ASSEMBLY, RECEPTACLE,
SLIMSEAL SSL CONNECTOR

SIZE
A200779

CAGE CODE
C-2106391

DRAWING NO
C-2106391

RESTRICTED TO
-

SCALE
4:1

SHEET
3

OF
3

REV
G