


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
FT	0					APVD
		Z2		REVISED PER ECO-14-006701	07MAY2014	NK
						DR



1

NYLON, UL 94V-0 RATED, RED.

2

BRASS PER ASTM B36.

3

3.81um [.000150] MIN TIN OVER 2.54um [.000100] MIN COPPER.

4

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

5

0.38um [.000015] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN-LEAD FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

6

.000150 MIN TIN OVER .000100 MIN COPPER OR .000050 MIN NICKEL.

7

0.76um [.000030] MIN GOLD FOR A LENGTH OF 5.08 [.200] FROM MATING END, 3.81um [.000150] MIN TIN FOR A LENGTH OF 4.83 [.190] MIN FROM OPPOSITE END, BOTH OVER 1.27um [.000050] MIN NICKEL.

OBSOLETE

OBSOLETE

11.79[.464]	4.60±0.64[.181±.025]	YES	7	NO	1-206763-4
11.79[.464]	4.60±0.64[.181±.025]	YES	7	YES	1-206763-3
11.79[.464]	4.60±0.64[.181±.025]	YES	6	NO	1-206763-2
11.79[.464]	4.60±0.64[.181±.025]	YES	6	YES	1-206763-1
11.79[.464]	4.60±0.64[.181±.025]	NO	5	YES	206763-9
13.31[.524]	4.60±0.64[.181±.025]	YES	3	NO	206763-8
11.79[.464]	4.60±0.64[.181±.025]	YES	4	NO	206763-4
11.79[.464]	4.60±0.64[.181±.025]	YES	4	YES	206763-3
11.79[.464]	4.60±0.64[.181±.025]	YES	3	NO	206763-2
11.79[.464]	4.60±0.64[.181±.025]	YES	3	YES	206763-1
B	A	LATCHES	CONTACT FINISH	MOUNTING TABS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.13 [.005]

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL HOUSING: 1

FINISH CONTACT: SEE TABLE

DWN L. SIPE 03/11/92

CHK R. STONE 3-17-92

APVD A. TRAVIS 3-17-92

NAME

PRODUCT SPEC 108-10033

APPLICATION SPEC

SIZE CAGE CODE DRAWING NO RESTRICTED TO

WEIGHT

SCALE 4:1 SHEET 1 OF 1 REV Z2

CUSTOMER DRAWING

TE Connectivity

PIN HEADER ASSEMBLY, 24 POSITION, METRIMATE

206763

4805 (3/11)