

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.


LOC
H

DIST
-





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	H3	APPLICATION SPECIFICATION NUMBER ADDED	24JUL2013	KJK	RP


REFERENCE MATING INTERFACE PATTERN:
1,27 STAGGERED PITCH x 1,5 ROW-DISTANCE.





POLARISATION SLOT




RECOMMENDED PC-BOARD
PAD-LAYOUT TOP VIEW




SECTION A-A




SCALE 3:1



SOLDER DETAIL
SCALE 10:1




EXAMPLE SOLDER JOINT



SEE DETAIL X

USER DIRECTION OF FEED

ACCORDING EIA-481/DIN IEC 286



POLARIZATION-SLOT
ON THIS SIDE.

DETAIL X
SCALE 1:1

NOTES:

- 1 TAPE FOR VACUUM P&P ONLY FOR DASH NUMBERS 7- /8- /9-
- 2 FOR PACKAGING SEE SHEET 2 AND 3
- 3 WITHOUT VACUUM TAPE.
- 4 CORING-OUTS FOR MANUFACTURING PURPOSE ONLY.
SHAPE MAY VARY, BUT IS NOT FUNCTIONAL FOR THE APPLICATION.
- 5 SHOWN IS A 10 POSITION CONNECTOR.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	±

MATERIAL SEE TABLE

3	PICK & PLACE TAPE	KAPTON	AMBER TRANSPARENT
2	FEMALE HOUSING	POLYAMIDE 4/6,GF	RED
1	FEMALE CONTACT	PHOSPHOR BRONZE	TIN OVER NICKEL
Item no.	Description	Material	Finish

DWN	M. Gosselink
CHK	-
APVD	-
PRODUCT SPEC	108-19052
APPLICATION SPEC	114-13318
WEIGHT	-



TE Connectivity

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, WITH LATCHES, Micro-MaTch

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-338069	-

CUSTOMER DRAWING SCALE 5:1 SHEET 1 OF 3 REV H3

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE

DWN

APVD


SEE SHEET 1




7-338069-4

4 POSITIONS

338069-4




24mm
wide tape




7-338069-6

6 POSITIONS

338069-6




24mm
wide tape




7-338069-8

8 POSITIONS

338069-8




24mm
wide tape




8-338069-0

10 POSITIONS

1-338069-0




44mm wide tape




8-338069-2

12 POSITIONS

1-338069-2




44mm wide tape




8-338069-4

14 POSITIONS

1-338069-4




44mm wide tape




8-338069-6

16 POSITIONS

1-338069-6




44mm wide tape



8-338069-8

18 POSITIONS

1-338069-8



44mm wide tape

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

M. Gosselink

CHK

-

APVD

-

PRODUCT SPEC

108-19052

APPLICATION SPEC

114-13318

WEIGHT

-

CUSTOMER DRAWING

TE

TE Connectivity

NAME

CONNECTOR,
FEMALE-ON-BOARD TOP-ENTRY,
SMD, WITH LATCHES, Micro-MaTch

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779


C-338069

SCALE 5:1


SHEET 2 OF 3

REV H3



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
H	-		-	SEE SHEET 1	-	-




9-338069-0
20 POSITIONS
2-338069-0



9-338069-4
24 POSITIONS
2-338069-4



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. Gosselink	IDEC01		 TE Connectivity						
DIMENSIONS: mm		CHK -	NAME CONNECTOR, FEMALE-ON-BOARD TOP-ENTRY, SMD, WITH LATCHES, Micro-MaTch								
		APVD -									
		PRODUCT SPEC 108-19052									
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		APPLICATION SPEC 114-13318	SIZE A3		CAGE CODE 00779	DRAWING NO C-338069	RESTRICTED TO -				
		WEIGHT -									
MATERIAL -		FINISH -		CUSTOMER DRAWING				SCALE 5:1	SHEET 3	OF 3	REV H3