






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		U2	REVISED PER ECO-13-017833	12FEB2014	NK	MZ

D

C

B

A




POST ARRANGEMENT ON REAR FACE

2 SUPERSEDED BY 1-207303-4

- CONNECTOR WILL ACCEPT POSTED TYPE III+ PIN CONTACTS.
- OBsolete PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- .000030 MIN PRECIOUS METAL PLATE ON MATING END FOR A LENGTH OF .200 MIN OVER .000050 MIN NICKEL PLATE. GOLD FLASH ALL OVER. CONFORMS TO THE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPEC 108-10042, BASED ON EIA/ECA-364-1000.01A (CONTROLLED ENVIRONMENTAL APPLICATIONS.)

NO	YES	TIN	3	.130	1-207303-7
NO	YES	TIN	3	.119	1-207303-6
NO	NO	TIN	TIN	.220	1-207303-5
NO	YES	TIN	3	.220	1-207303-4
NO	NO	TIN	3	.220	1-207303-3
YES	NO	TIN-LEAD	3	.220	1-207303-2
NO	YES	TIN-LEAD	GOLD	.220	1-207303-1
NO	NO	TIN-LEAD	3	.220	207303-3
NO	NO	TIN-LEAD	TIN	.220	207303-1
PERIPHERAL SEAL	THREADED INSERTS	CONTACT POST FINISH	CONTACT BODY FINISH	A	PART NUMBER

RECOMMENDED P.C. BOARD LAYOUT
BOTTOM NON-COMPONENT SIDE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.LEE BG 7-2-91	 TE Connectivity			
DIMENSIONS: INCHES		CHK W.G.LENKER 4-14-92				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ± 2'	APVD -	NAME RECEPTACLE ASSEMBLY, POSTED, STD SEX, SERIES 1, 17-16, CPC			
		PRODUCT SPEC 108-10024				
		APPLICATION SPEC -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO -
		MATERIAL SEE CALLOUT	FINISH SEE TABLE	WEIGHT -	A2	
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV U2	