




LOG		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
G		14								G		REV PER 0G3A-0031-04		29JAN04		MS	

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	E13288 Listed
22-16 AWG SOLID OR STRANDED	22-16 AWG SOLID OR STRANDED
LR7189 Certified	MILITARY P/N AND CLASS
22-16 AWG SOLID OR STRANDED	M7928/7-6 CLASS 2 P/N 34115 & 2-34115-2 ONLY

- 1 STAMP AMP 22-18* APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN
ACCORDANCE WITH MILITARY SPECIFICATION
MIL-T-7928; COMMERCIAL WIRE RANGE IS 22-16
- 2 TIN PLATE .000100 MIN THK PER ASTM B-545
- 3 NICKEL PLATE .000300 MIN THK PER QQ-N-290
- 4 P/N 34115-1 IS NOT UL OR CSA APPROVED

3	---	LOOSE PIECE	4	34115-1
2	100	LOOSE PIECE, BOX		8-34115-1
2	5000	ON TAPE		2-34115-2
2	---	LOOSE PIECE		34115
FINISH		QUANTITY	PACKAGING TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C MAX	DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 3-10-93 TA BRINKMAN	AMP AMP Incorporated Harrisburg, PA 17105-3608				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE	MATERIAL COPPER PER ASTM B-152 ANNEALED	CHK 3-10-93 DA PATTERSON	NAME TERMINAL, RING TONGUE, SOLISTRAND				
		WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm² [509-3,260] CIR MILS SOLID OR STRANDED		APPD 3-10-93 DE MILLER					
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	FINISH SEE TABLE	APPD 3-10-93 JL MECKLEY				PRODUCT SPEC -	APPLICATION SPEC -
FOR ORDER ENTRY	1-800-526-5142			WEIGHT -	SCALE 8:1	SHEET 10F 1			