





NUMBER 917337



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST



推奨基板取付け寸法

PC 基板厚: 1.6±0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN

PC BOARD THICKNESS: 1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER (94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 0.76μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN LEAD PLATED (CONTACT TAIL) OVER NICKEL
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL
- THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE THEY DON'T SHOW DETAILS
- THE DATE CODE SHOW PRODUCTION LOT BY NUMBER. THE NUMBER MAKE UP THE NUMBER OF FOUR COLUMNS OR FIVE COLUMNS. (INCLUDE THE ALPHABET)

注記

- 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂 (94V-0), 色: 黒
コネクタ: 銅合金
- リテンションレグ: 銅合金
- めっき: コネクタ: 全面Ni下地
接触部: 0.38μm MIN 金めっき
- めっき: コネクタ: 全面Ni下地
接触部: 0.76μm MIN 金めっき
- めっき: コネクタ: 全面Ni下地
接触部: 2.0 μm MIN スズめっき
- めっき: リテンションレグとコネクタ半田付部
ニッケル下地の土に半田めっき
- めっき: リテンションレグとコネクタ半田付部
ニッケル下地の土にスズめっき
- 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません
- 4桁の数字及びアルファベットを含む5桁の数字により製造ロットを示す。

	Y	6	4	2-917337-5
	X	6	3	2-917337-3
	X	6	2	2-917337-2
	X	6	4	1-917337-5
	X	6	3	1-917337-3
	X	6	2	1-917337-2

キーイング KEYING LOCATION	キーイング KEYING	FINISH	製品番号 PART NO.
WIRE RANGE	INSULATION DIA	NAME	
mm (AWG)	mm	ダイナミック D-3200S 5.08 ピッチ (V) 2 極 ヘッダーアセンブリ	
MATERIAL	FINISH	DYNAMIC D-3200S 5.08 PITCH (V) 2 POS. HDR. CONN. ASS'Y	
SEE NOTES 注記参照	SEE NOTES 注記参照		
DR. 18/OCT/94	DE. 18/OCT/94	一般公差 (GENERAL TOLERANCE)	SIZE LOC NUMBER
CHK. K. IKEDA	APP. K. IKEDA	10% : ±0.3 30% : ±0.4 100% : ±0.45 角度 : ±3°	A3 J C-917337
B2	REVISED PER ECO-11-005030	RK	HMR
LTR	REVISION RECORD	DR	CHK
DATE		DATE	
19 OCT 94		19 OCT 94	
S. MANABE		S. MANABE	
SCALE		REV. B2	
2-1		SHEET 1 OF 1	