






NUMBER 178314



METRIC

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT DIST

AMP-J
REV.10/93

推奨基板取付け寸法

PC 基板厚: 1.6±0.1
(非累積公差)
(コネクタ搭載面)

RECOMEND PC BOARD HOLE PATTERN


PC BOARD THICKNESS: 1.6±0.1
(NOT ACCUMULATE TOLERANCE)
(CONNECTOR MOUNT SIDE)

NOTES

- MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC, POLYESTER
CONTACT: COPPER ALLOY
RETENTION LEG: COPPER ALLOY
- FINISH (CONTACT AREA): 0.38μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 0.76μm MIN GOLD PLATING OVER Ni PLATING
- FINISH (CONTACT AREA): 2.0 μm MIN TIN PLATED OVER NICKEL
- FINISH (RETENTION LEG): TIN-LEAD PLATED (CONTACT TAIL) OVER NICKEL
- FINISH (RETENTION LEG): TIN PLATED (CONTACT TAIL) OVER NICKEL
- THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE THEY DON'T SHOW DETAILS
- THE DATE CODE SHOW PRODUCTION LOT BY NUMBER. THE NUMBER MAKE UP THE NUMBER OF FOUR COLUMNS OR FIVE COLUMNS. (INCLUDE THE ALPHABET)

注記

- 材料: ハウジング: ガラス入り熱可塑性ポリエステル樹脂
コンタクト: 銅合金
リテンションレグ: 銅合金
- めっき: コンタクト: 全面Ni下地
接触部: 0.38μm MIN金めっき
- めっき: コンタクト: 全面Ni下地
接触部: 0.76μm MIN金めっき
- めっき: コンタクト: 全面Ni下地
接触部: 2.0 μm MINスズめっき
- めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上に半田めっき
- めっき: リテンションレグとコンタクト半田付部
ニッケル下地の上にスズめっき
- 文字の形状、大きさ、および位置については、大略を示すものであり、詳細を示すものではありません
- 4桁の数字及びアルファベットを含む5桁の数字により製造ロットを示す。



6	4	1,2-178314-5
6	3	1,2-178314-3
6	2	1,2-178314-2
(FINISH)		製品番号 (PART NO.)

D2	REVISED	Y.O.T.K.	19 OCT 2009
D1	REVISED (ECR-08-027321)	T.S.A.O.	29 OCT 2008
D	REVISED (ECR-07-020412)	Y.Y.D.M.	28 AUG 2007
C	REVISED (FJD0-0039-03)	T.S.S.M.	2 JUN '03
B	REVISED (FJD0-0114-03)	T.S.S.M.	25 APR '03
A	REVISED (FJ00-2183-95)	K.I.S.M.	3-23 '95
O	RELEASED (FJ00-1468-94)	K.I.S.M.	10/JAN '95
LTR	REVISION RECORD	DR	CHK

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.		Tyco Electronics Tyco Electronics Corporation Kawasaki, Japan	
WIRE RANGE	INSULATION DIA	NAME	
mm² (AWG)	mmφ	ダイナミック 3100 シリーズ 4極 ヘッダーアセンブリ (垂直タイプ) 4 POS SINGLE ROW VERTICAL HDR ASS'Y FOR DYNAMIC 3100	
MATERIAL	FINISH	一般公差 (GENERAL TOLERANCE)	SIZE LOC NUMBER
SEE NOTE 注記参照	SEE NOTE 注記参照	10mm ±0.3 10mm 30mm ±0.4 30mm 100mm ±0.45 角 度 ±3°	A3 J C-178314
DR. K.IKEDA 22/DEC/94 S.MANABE 10/JAN/95	DE. K.IKEDA 22/DEC/94 APP. S.MANABE 10/JAN/95	SCALE 2-1	REV. D2 SHEET 1 OF 1

(CUSTOMER DRAWING) 顧客用図面