

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - new logo 2011

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

H

-

P

LTR

DESCRIPTION

DATE

DWN

APVD

F

CHANGES PER ECR-11-006548

21OCT2011

PP

JK

G

CHANGES PER ECR-12-004118

02MAR2012

PP

JK

G1

CHANGES PER ECR-13-013257

30AUG2013

RS

DD

G2

CHANGES PER ECR-14-011255

01AUG2014

RS

DD

NOTES:



CONNECTOR ACCEPT MULTIPLE WIRES SIZES: SEE TABLE.

2

HOUSING AND BUTTON MATERIAL : POLYCARBONATE

3

IDC CONTACT MATERIAL: PhBR









PRINTING LOGO'S: P/N 293545-1 and -2: UL, ENEC, KEMA, PARTNUMBER, TE.



PRINTING LOGO'S: P/N 293545-3 and -4: UL, PARTNUMBER, TE.

6

WIRE INSULATION DIAMETER
RANGE IS FROM 1.75 TO 2.85 mm




SEE NOTE 4 & 5

YELLOW TRANSPARENT	293545-4	5	SPLICING CONNECTOR SEALED	AWG 20 (0.52mm ²) / AWG 22 (0.33mm ²)
	293545-3	5	SPLICING CONNECTOR UNSEALED	AWG 20 (0.52mm ²) / AWG 22 (0.33mm ²)
CLEAR	293545-2	4	SPLICING CONNECTOR SEALED	AWG 18 (0.82mm ²) TO 0.75mm ²
	293545-1	4	SPLICING CONNECTOR UNSEALED	AWG 18 (0.82mm ²) TO 0.75mm ²
HOUSING COLOR	PARTNUMBER	DESCRIPTION		CABLE SIZE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.2
2 PLC ±0.15
3 PLC ±
4 PLC ±
ANGLES ±3°

MATERIAL

SEE NOTES

SEE NOTES

DWN 04MAR2010

CHK J.v.d.Krogt 04MAR2010

APVD J.v.d.Krogt 06MAR2010

PRODUCT SPEC

108-19419

APPLICATION SPEC

114-19136

WEIGHT

-

Customer Drawing



TE Connectivity

SPLICING CONNECTOR

NAME

-

-

SIZE

A3

CAGE CODE

00779

DRAWING NO

C-293545

RESTRICTED TO

-

SCALE

2:1

SHEET

1

OF

1

REV

G2