

REV.	ECN NO.	DATE	SGN	DESCRIPTION

1

2

3

4

5

6

7

8

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

Amphenol LTW

DCC. DEPT.

CONFIDENTIAL

2007.03.01

ISSUED

1

2

3

4

5

PG16

M25*1.5

32.0(REF.)

LTW

49.6(REF.)

15.0

Section A-A

PG16

LTW

Note:

* Waterproof Rate: IP68

* Screw Nut:Nylon,Black

* Clamp Ring:Nylon,Black

* Sealing Nut:Nylon,Black

* Gasket:EPDM,Black

* Seals:EPDM,Black

* Cable Range: ϕ 10.0~ ϕ 14.0mm

* For Panel Thickness:6.0mm max

* Spanner Size:

Body: 27.2mm

Sealing Nut: 29.0mm

Screw Nut: 28.5mm

UNIT:mm

TOLERANCE

X
XX
XXX

ANGLES

± 0.25
 ± 0.1
 ± 0.05

$\pm 1^\circ$

Cable Gland for PG16,Black (Long)

SCALEFree

REV.A

SHEET1

OF1

Inspection Item

ITEM NO

CSG-16G001

DWG NO

CSG-16G001

CUSTOMER

ALTW

DRAWN BY

Tina

CHECKED BY

Liu

APPROVED BY

Liu yangzhi

DATE

2006/12/26

DATE

2007/01/11

DATE

2007/01/11