






2		1					
LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A	RELEASED	23JUL2014	J. J	W. H




3D VIEW
ONLY FOR REFERENCE

TE P/N	DIM A	DIM B	DIM H	DIM I	WORK RANGE	QUANTITY
3-2199250-2	2.9	1.9	2.86	2.44	2.0~2.7	5000
3-2199250-3	3.2	2.2	2.87	2.44	2.3~3.0	4400
3-2199250-4	3.6	2.6	2.92	2.45	2.6~3.3	3000
3-2199250-5	3.8	2.8	2.95	2.46	2.9~3.6	3000




- 1 PART NUMBER: SEE TABLE.
2 MATERIAL: COPPER ALLOY, THICKNESS=0.10MM.
3 PLATING: 2um MIN. NICKEL UNDERLAYER ALL OVER
0.50um MIN. GOLD ON CONTACT SURFACE
GOLD FLASH ON SOLDERING SURFACE

4 PICK AND PLACE SURFACE Ø1.2MM.



PROFILE OF
SPRING FINGER

OUTLINE OF
KEEP OUT AREA



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TONY ZHANG 24MAY2013	TE Connectivity			
		CHK WENKE HE 24MAY2013				
		APVD WENKE HE 24MAY2013	NAME SPRING FINGER TYPE C			
DIMENSIONS: mm		PRODUCT SPEC 108-115061-1				
		APPLICATION SPEC -				
MATERIAL 2		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO C-2199250	RESTRICTED TO -
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.2 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.10 4 PLC ± ANGLES ±5° FINISH 3		CUSTOMER DRAWING	SCALE N/A	SHEET 1	OF 2	REV A

