






REVISIONS					
P.	LTR.	DESCRIPTION	DATE	DWN.	APVD.
	C	REVISED PER ECO-14-005095	15APR2014	AP	RP



RECOMMENDED PC BOARD LAYOUT,
DAUGHTER BOARD,
COMPONENT SIDE SHOWN
SCALE 5:1

- REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
- MATERIAL:
SHIELD - PHOSPHOR BRONZE
CONTACT - COPPER-NICKEL-SILICON
HOUSING, CHICKLET AND CHICKLET COVER - GLASS FILLED POLYESTER, UL 94V-0 RATED.
- FINISH: CONTACT AND SHIELD
MATING AREA:
MEETS THE PERFORMANCE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPECIFICATION, 108-2055-1; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA:
0.5µm MIN BRIGHT TIN/LEAD OVER BASE PLATING.
- CONNECTOR MARKED WITH PART NUMBER AND DATE CODE IN APPROXIMATE AREA SHOWN.
- DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERANCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- FINISH: CONTACT AND SHIELD
MATING AREA:
MEETS THE PERFORMANCE REQUIREMENTS OF TYCO ELECTRONICS PRODUCT SPECIFICATION, 108-2055-1; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
COMPLIANT PIN AREA:
0.5µm MIN MATTE TIN OVER BASE PLATING.



3	2065769-2
8	2065769-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. J. MAGARO 08MAY2009	TE Connectivity	
DIMENSIONS:		CHK S. J. MAGARO 08MAY2009		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD N. SCHROLL 08MAY2009	NAME	
	0 PLC ±	PRODUCT SPEC	ASSEMBLY, Z-Pack HMZd Plus, RECEPTACLE, 2 PAIR	
	1 PLC ±	APPLICATION SPEC		
	2 PLC ±		SIZE CAGE CODE DRAWING NO	
	3 PLC ±		A100779C=2065769	
	4 PLC ±		RESTRICTED TO	
	ANGLES ±	WEIGHT	SCALE 8:1 SHEET 1 OF 1 REV C	
MATERIAL	FINISH	CUSTOMER DRAWING		