




CONTACT CHARACTERISTICS

MATERIALS:

- A. CONTACTS: INNER-COPPER ALLOY, GOLD PLATED PER MIL-G-45204 OVER NICKEL UNDERPLATE
OUTER-COPPER ALLOY, SELECTIVELY GOLD PLATED PER MIL-G-45204 AND TIN PLATED PER MIL-T-10727 OVER NICKEL UNDERPLATE.

B. SOLDER: SN 63 PER QQ-S-571

C. TUBING: POLYVINYLIDENE FLUORIDE

D. DIELECTRIC: FLUOROPOLYMER

PERFORMANCE:

- A. MAXIMUM OPERATING TEMPERATURE: 125° C.
- B. HIGH POTENTIAL, RATED, SEA LEVEL: 600 VRMS AT 60 Hz.
- C. CURRENT RATING: 3 AMPS MAX.
- D. INSULATION RESISTANCE: 5 GIGAOHMS MIN.
- E. CONTACT RESISTANCE: 12 MILLIOHMS MAX.
- F. CONTACT RETENTION IN CONNECTOR: 18 LBS.(8.1 KILOGRAMS) MIN.
- G. ENGAGEMENT FORCE, OUTER SOCKET: 10.0 OZ. (280 GRAMS) MAX.
[.074 (1,880) DIA. PIN.]
SEPARATION FORCE, OUTER SOCKET: 0.75 OZ. (21 GRAMS) MIN.
[.072 (1,829) DIA. PIN.]

NOTES

- 1. THIS CONTACT IS DESIGNED TO TERMINATE TO THE CABLES IN THE FOLLOWING TABLE:

RG CABLE NO.	RAYCHEM CABLE NO.
RG-174 U	5024A IXIX
RG-178 B/U	5028A IXIX
RG-179 B/U	5030A IXIX
RG-316 U	7528 A IXIX
	7530A IXIX
	9532 A IXIX

OTHER APPLICATIONS SHOULD BE SUBMITTED TO RAYCHEM FOR EVALUATION.

- 2. FOR TERMINATION PROCEDURE SEE ES 61170
- 3. MATING CONTACT (FOR SIMILAR CABLES): D-602-0278

- 4. THIS CONTACT IS DESIGNED TO BE USED IN THE CAVITY DETAILED ABOVE.

SPECIFICATION CONTROL DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES BRACKETED DIMENSIONS () ARE METRIC AND TOLERANCES ARE: XXX ± () XX ± () Δ ±	DRAWN	CERDAN 3-12-85	tyco Electronics Tyco Electronics Corporation 300 Constitutional Drive Menlo Park, CA 94025 USA Raychem
	CHECKED		
	APPROVED	3-12-85	
	APPROVED		
TITLE			SUBMINIATURE COAX CONTACT SOCKET
SIZE C CODE IDENT NO. 06090 DWG NO. D-602-0279			
DO NOT SCALE THIS DRAWING			WEIGHT — SHEET 1 OF 1

If this document is printed it becomes uncontrolled.
Check for the latest revision.