



REV	ECCO No.	REVISION	DR	CK	AP	DATE
A	NONE	ENGINEERING RELEASE	GH			09/14/99
B	7028	CHANGE KICK GUARDS	LS		DK	28 MAY 02
C	7699	UPDATED FRONT PANEL	LW		DK	10 OCT 03
D	7907	COR. VOLTAGE RATINGS	LW		DK	28 MAY 04
E	8240	CHANGE TO BLACK CHASSIS	J.O.			19 DEC 05



- RACK MOUNTED, STEEL CHASSIS, BLACK MEDIUM TEXTURE
19.00" WIDTH STANDARD RACK MOUNTING
1.72" HEIGHT.
7.00" DEPTH
NOTE: CHASSIS SUPPORT BRACKETS OR SLIDES ARE REQUIRED
- INPUT: 110-125 VAC OR 200-240 VAC, VOLTAGE SELECTABLE
SINGLE-PHASE, 50/60 HZ.
16 AMP MAXIMUM TOTAL CURRENT.
POWER INLET: IEC 320 C-20 INLET, RATED 16/20 AMP.
- OUTPUT: 110-125 VAC OR 200-240 VAC, 12 IEC 320 C-13 RECEPTACLES,
4 OUTLETS PER SECTION, NO TIME DELAY BETWEEN EACH SECTION.
16 AMPS MAXIMUM TOTAL CURRENT.
- CIRCUIT BREAKER: ONE 2-POLE, 20 AMP MAIN POWER,
MAGNETIC, WITH HIGH INRUSH TIME DELAY.
- INDICATOR LIGHT: 2 GREEN, ONE PER VOLTAGE RANGE,
ON WHEN MAIN CIRCUIT BREAKER IS ON.
3 GREEN, ONE FOR EACH SECTION.
- FILTER: EM/RFI, 20AMP RATED, 50/60 HZ.
COMMON MODE, LINE TO GROUND
DIFFERENTIAL MODE, LINE TO LINE
- SPIKE & SURGE PROTECTION: LINE TO LINE
- REMOTE I/O SWITCHING CONNECTOR
MATES WITH AMP # 1-480305-0 CONNECTOR
WITH AMP # 60620-1 PINS.




NOTE: THIS UNIT IS DESIGNED FOR REMOTE OPERATION. EVEN WHEN THE "REMOTE/OFF/LOCAL" SWITCH IS SET TO "LOCAL" THE UNIT STILL REQUIRES A POWER REQUEST FROM THE REMOTE PORTS.

REMOTE START REQUIRES TWO CONDITIONS:
1) MAINTAINED CONTACT BETWEEN PINS 2 & 3
2) MOMENTARY CONTACT BETWEEN PINS 1 & 3

REMOTE POWER OFF/EPO REQUIRES OPENING OF MAINTAINED CONTACT BETWEEN PINS 2 & 3. THIS TURNS OFF SWITCHED OUTLETS REGARDLESS OF REMOTE SWITCH POSITION.

FOR START UP OF ADDITIONAL LATCHING UNITS, CONNECT PINS 1 & 2 ON J3 (SEQUENCE PORT) TO ANY REMOTE PORT ON ANOTHER LATCHING UNIT. DO NOT CONNECT TO ANOTHER SEQUENCE PORT. SEQUENCE PORT ACTIVATES 4 SECS AFTER "SW 3" OUTLETS TURN ON.

- UL RECOGNIZED COMPONENTS WHERE APPLICABLE.



THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF PULIZZI ENGINEERING INC. PULIZZI ENGINEERING INC. RESERVES ALL PATENT, PROPRIETARY DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERETO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2003 P.E.L.

PULIZZI ENGINEERING INC.
3200 S. Susan Street, Santa Ana, CA 92704
(714) 540-4229 Fax (714) 641-9062

ENGINEERING DRAWING
TPC2365-LT ASSY 3090

SCALE: 1:1 SHEET: 1 OF 1
DRAWN BY: ON
DATE: 09/14/99

CAGE CODE: 70513
REV: E