


HONEYWELL PART NUMBER
13SX96-T
PRODUCT CODE VDK2843

REV	DOCUMENT	CHANGED BY	CHECK
6	0060324	VKR 13JAN10	CMH

B

A

A



- NOTES
- MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF $\phi .087$ MAX ON $.188 \pm .002$ CENTERS
 - TERMINALS ARE SOLDER DIPPED WITH ROHS-COMPLIANT TIN/COPPER/SILVER SOLDER.
 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
 - PLUNGER WILL BE FLUSH TO UNDERFLUSH AT FULL OVERTRAVEL

RELEASE NO.	PR-22522
REPLACES	X100695-SX

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ±		DRAWN	SPK	15FEB08	Honeywell				
OPERATING FORCE — — — 6 OZ MAX		CONTACT ARRANGEMENT SPDT					CHECK	RJ	15FEB08					
RELEASE FORCE— — — — 1/2 OZ MIN		30 VOLTS DC RATING			.030 .015 .005		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .001 MAX			SEA LEVEL	50,000 FT										
OVERTRAVEL — — — — — .010 MIN		INDUCTIVE	0.5 AMP	0.5 AMP			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
RESISTIVE			1 AMP	1 AMP						B	I	13SX96-T		6
MAXIMUM INRUSH 2 AMP					THIRD ANGLE PROJECTION 		RASTER			SCALE	-	WEIGHT:.003 LB MAX	SHEET 1 OF 1	
APPROVALS	KEMA, CE	1A 250 V ~ T125 25E3												
	UL, CSA	1A 125 VAC BRAND L22J												