NOTES:

I. MATERIALS AND FINISHES:

BODY - BRASS, NICKEL PLATING CONTACT - BRASS, SILVER PLATING

INSULATOR - CO-POLYMER OF STYRENE, NATURAL

2. ELECTRICAL:

A. IMPEDANCE: 50 OHM

B. VSWR: I.3 MAX.

C. FREQUENCY RANGE: DC 0-300 MHz

D. DIELECTRIC WITHSTANDING VOLTAGE: 1500 VRMS, MIN.


3. MECHANICAL:

A. DURABILITY: 500 CYCLES MIN.


B. TEMPERATURE RANGE: - 55°C to +85°C

THIRD ANGLE PROJ. 🕀 🖯

REV	DESCRIPTION	DATE	ECO	APPR
М	ADDED NOTES 2 THRU 7	2-23-93	39230	DR
N	ADD COD SHEFT	16-0ct-12	49076	SH



SCALE 1.500



CUSTOMER OUTLINE DRAWING

ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: <0.5mm 0.5 - 6mm 6 - 30mm 30 - 120mm ANGLES ±0.05mm ±0.1mm ±0.2mm ±0.3mm ±1°	MATERIAL -	DRAWN R.MAO	DATE II-Jun-I2	TITLE ADAPTER-UHF FEMALE	Amphenol RF	
NOTICE - These drawings, specifications, or other data (I) are, and remain the property of Amphenol corp. (2) must be returned upon requiest; and (3) arre confidential and not to be disclosed to any person other than those to whom they		ENGINEER S.HSIEH	DATE II-Jun-I2	N MALE UG-146/U	www.amphenolrf.com	
are given by Amphenol Corp. the funishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is	REFERENCE	APPROVED	DATE		DRAWING NO. 4400	
not to be regarded by implicatioin or otherwise in any manner licensing, granting rights to permitting such holder or any other sperson to manufacture, use or sell any	CONFIGURATION LEVEL:	S. HSIEH	11-Jun-12	SCALE: 3.0:1.0 SHEET 2 OF 2	ITEM NO. 4400	
product, process or design, patented or otherwsie, that may in any way be related to or disclosed by said drawings, specifications, or other data.	FINISH	CAD FILE		DWG SIZE REV R	PART NO. 4400	