

CATALOG LISTING
BZ-2RQ1008-A2

ISSUE
6

REVISIONS	
A	CO-76742 LJF 2 MAR 94
B	CO-77589 LJF 31 MAR 94
C	CO-77853 MAM 17 AUG 94
D	CO82133 J A K 30 JUL 96
E	CO93346 DLT 12 AUG 98

DDM/CAD
DRAWN
LJF

REPLACES X97331-BZ
RELEASE NO. PR-20635
CHECK
18 AUG 93
20 AUG 93
J W B
18 AUG 93


MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RQ1008-A2




NOTE
 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
 2 HARDWARE FURNISHED UNASSEMBLED

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE ----- 5 OZ MAX		CONTACT ARRANGEMENT S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ± WEIGHT .094 LB	
RELEASE FORCE ----- 2 1/2 OZ MIN		L9			
DIFFERENTIAL TRAVEL --- .0004-.002		10A 125, <u>250</u> OR 480 VAC			
OVERTRAVEL ----- .219 MIN		1/2A 125 VDC, 1/4A 250 VDC			
OVERTRAVEL FORCE ----- 10 OZ MAX		L288			
		  			