

Customer Information Sheet


DRAWING No.: M50-365XX42R SHEET 3 OF 4

IF IN DOUBT - ASK (C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$

ANGLES = $\pm 5^\circ$

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE: 1.27mm DIL SMT EJECTOR
HEADER WITH CAP & PEGS
TAPE & REELED

DRAWING NUMBER:

M50-365XX42R

SHT

3




OF

4


Customer Information Sheet

SPECIFICATIONS:
MATERIALS:
MOULD = LCP, 30% G/F, UL94V-0
CONTACT = BRASS
FINISH:
42 = 0.015-0.02µ GOLD ON CONTACTS,
2.54µ 100% TIN ON TAILS OVER,
0.76-2.03µ NICKEL
ELECTRICAL:
RATED CURRENT = 1.75A
CONTACT RESISTANCE = 20mΩ MAX
WITHSTAND VOLTAGE = 1000V ACrms/DC FOR 1 MIN
INSULATION RESISTANCE = 5000MΩ MIN
ENVIRONMENTAL:
OPERATING TEMPERATURE = -55°C TO +125°C
FOR COMPLETE SPECIFICATION, SEE COMPONENT
SPECIFICATION C029XX (LATEST ISSUE)

ORDER CODE: **M50-365XX42R**
No.OF CONTACTS PER ROW:
05, 06, 07, 08, 10,
13, 17, 20, 25
FINISH:
SELECTIVE GOLD, TIN



- NOTES:
1. CAP REMOVED FROM MAIN VIEWS FOR CLARITY, PART COMES WITH CENTRALLY FITTED CAP.
2. ALL TOLERANCES ARE ± 0.25 UNLESS OTHERWISE STATED.
3. ALL COMPONENTS ARE RoHS AND REACH COMPLIANT.



SB	6	14.10.15	13049
NAME	ISS.	DATE	C/NOTE
APPROVED: S.BENNETT			
CHECKED: M.PLESTED			
DRAWN: R.ADDE			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN
www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES
X = $\pm 1\text{mm}$
X.X = $\pm 0.50\text{mm}$
X.XX = $\pm 0.10\text{mm}$
X.XXX = $\pm 0.01\text{mm}$
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:	SEE ABOVE
FINISH:	SEE ABOVE
S/AREA:	mm ²

TITLE: 1.27mm DIL SMT EJECTOR HEADER WITH CAP & PEGS TAPE & REELED	
DRAWING NUMBER: M50-365XX42R	SHT 4 OF 4