








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	ECN-0503095	2005/03/21	XL M	Ref. To ECN.Note



Note:

- * Cable Range: $\phi 6.0 \sim \phi 10.0 \text{mm}$
- * 適用線徑: $\phi 6.0 \sim \phi 10.0 \text{mm}$
- * For Panel Thickness Max 7.5mm
- * 適用板厚: 7.5mm
- * Color: Black
- * 顏色: 黑色
- * @@ Important Dimension.
- * (@@ 為重點檢驗尺寸)

5	Sealing Nut	Black	Nylon	1	ANC173XXX01
4	Seals	Black	EPDM	1	DGA0030EP70
3	Clamp Ring	Black	Nylon	1	ANC350AXX01
2	Gasket	Black	EPDM	1	DGA0071EP70
1	Nut	Black	Nylon	1	ANC292AXX01
NO.	NAME	COLOR	SPECIFICATION	QTY	NOTE

UNIT:mm			
TOLERANCE			
.X ±0.25			
.XX ±0.1			
.XXX ±0.05			
ANGLES ±1°			
1			

TITLE			
PG9 Cable Glands Assembly			
SCALE		1 / 1	
REV. B		SIZE A4	
		SHEET 1 OF 1	
		QC : Inspection Item	

Amphenol LTW			
安費諾亮泰企業股份有限公司			
4		5	

ITEM NO		CSG-09G001	
DWG NO		CSG-09G001	
CUSTOMER		AL TW	
APPROVED BY		Steven Chen	
DATE		2005/03/21	

DRAWN BY		XL M	
CHECKED BY		Wu Dong	
DATE		2005/03/21	
APPROVED BY		Steven Chen	
DATE		2005/03/21	

8 FMW0702-01-	
---------------	--