

MATERIALS AND FINISHES

BODY, COUPLING NUT: BRASS
PLATED SEE TABLE


CRIMP TUBE: BRASS
PLATED NICKEL

CENTER CONTACT: BRASS
PLATED GOLD







INSULATOR: TEFLON

SHRINK TUBE: VERSAFIT

C'RING: BERYLLIUM COPPER




0.13±0.13
.005±.005
CONTACT/
INSULATOR




NOTE:
IF SHRINK TUBE INCLUDED
PLACE ONTO CABLE FIRST.

SEE SD-73251-942 FOR MORE P/N



73251-0457 & -0458 IS FOR
LMR100A OR EQUIVALENT
PLACE INNER FOIL LAYER
INSIDE REAR BODY



73251-0459	WITH HEAT SHRINK TUBE/PACKED STANDARD TRAY	GOLD 1u"/1u"	1.613 / .0635
73251-0458	NO HEAT SHRINK TUBE/PACKED STANDARD TRAY	GOLD 10u"/1u"	1.627 / .0680
73251-0457	WITH HEAT SHRINK TUBE/PACKED STANDARD TRAY	GOLD 10u"/1u"	1.627 / .0680
73251-0456	73251-0450 PACKED ONE PIECE PER BAG	GOLD 10u"/1u"	1.613 / .0635
73251-0455	73251-0453 PACKED IN SMALL TRAY (20 CAVITY)	NICKEL	1.613 / .0635
73251-0454	WITHOUT SHRINK TUBE/PACKED STANDARD TRAY	NICKEL	1.613 / .0635
73251-0453	WITH SHRINK TUBE/PACKED STANDARD TRAY	NICKEL	1.613 / .0635
73251-0452	73251-0450, PACKAGED IN SMALL TRAY (20 CAVITY)	GOLD 10u"/1u"	1.613 / .0635
73251-0451	WITHOUT SHRINK TUBE/PACKED STANDARD TRAY	GOLD 10u"/1u"	1.613 / .0635
73251-0450	WITH HEAT SHRINK TUBE/PACKED STANDARD TRAY	GOLD 10u"/1u"	1.613 / .0635
PART NO.	DESCRIPTION	FINISH	MM / IN
		BODY/NUT	DIM A

PS-89675-3460	PRODUCT SPECIFICATION
MIL-STD-348A, FIG. 310.1	INTERFACE
SPECIFICATION	DESCRIPTION
DIMENSION STYLE MM/IN	SCALE INCH
DRAWN BY TEF	DATE 2000/11/09
CHECKED BY SSS	DATE 2000/11/09
APPROVED BY GMH	DATE 2000/11/09
MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-73251-045
SHEET NO. 1 OF 1	

CHG: UPDATED VIEW
ADDED MORE P/N

EC NO: URF2015-0189
DRWN: JLE02
CHKD: SSS
APPR: WSPINK

QUALITY
SYMBOLS
▽=0
▽=0

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 2 °

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM/IN

DRAWN BY
TEF

CHECKED BY
SSS

APPROVED BY
GMH

MATERIAL NO.
SEE TABLE

SIZE
C

SCALE
INCH

DESIGN UNITS
INCH

THIRD ANGLE
PROJECTION

SMA PLUG STRAIGHT
RG-316 50 OHM
SMA-PC EWR-1766

MOLEX INCORPORATED

DOCUMENT NO.
SD-73251-045

SHEET NO.
1 OF 1