

		1	2 3			4	5	6
	PIN STYLE 01 02	MATING 5.9 8						
	03	9.9						
	05 06	9.2 10.4						
<u>A</u>	07 09	5.3 17.00						A
	10	8.10 8.50						
	12 13 14	3.05 14.35 4.00						
FG FC FC Page Page FC FC FC Page Page Page PC	4 = 2μm TIN 5 = 0.25μm 8 = 0.38μm	MIN FULL PLATED GOLD/GXT ON CONTAC GOLD/GXT ON CONTAC	CT AREA, 2µm TIN MIN ON TAIL CT AREA, 2µm TIN MIN ON TAIL CT AREA, 2µm TIN MIN ON TAIL R FOR ALL PLATING VERSIONS					В
Copyright FCI	2.54 TYP				mat'l. code Ltr ecn no dr date N F08-0253 LMU 08.12.1 P B-18789 LMU 14.09.1	ISO 1302 \ \ ISO 406 ISO 1101 tolerances unless otherwise specified	projection product family title	HR.HEADER
	2.54 TYP RECC	MMENDED PAD LAYOUT	<u> </u>		R B-18983 LMU 14.10.0 S B-20276 LMU 15.02.1 T B-20561 AMA 15.03.2	16 dr D.I.F 01.01.24	FC), dwg no 95	DR SMT sheet 2 of - size 5278 A3 STOMER Drawing
D	form: A3	1	2	3 PDS: Rev :V	sheet revision index sheet she	4 inted: Mar 27, 2015	5	D 6