









D

C

B

A



5	PICK&PLACE ADAPTOR	POLYAMIDE	NA	1	-	1	1	1
4	HOLD DOWN	DIN1544 CK75	5,0 μ m Sn MIN OVER 2,5 μ m Ni MIN ALL OVER.	2	2	2	2	2
3	CONTACT DETECTION	COPPER ALLOY	0,8 μ m Au MIN. IN CONTACT PLACE, Au FLASH IN SOLDER AREA OVER 1,27 μ m Ni MIN ALL OVER	-	4	-	-	4
2	CONTACT POWER TAB	COPPER ALLOY	1,2 μ m Ni MIN. ALL OVER 0,8 μ m Au MIN AT MATING ZONE 0,1-0,15 μ m Au AT SOLDER ZONE	2	-	2	-	-
2	CONTACT POWER TAB	COPPER ALLOY	3,0 μ m Ag MIN ALL OVER.	-	2	-	2	2
1	HOUSING	LCP GF UL94V-0	NA	1	1	1	1	1
ITEM NO.	DESCRIPTION	MATERIAL	FINISH	QTY	QTY	QTY	QTY	QTY

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN R. Annakkee 02-Apr-15 CHK R. Annakkee 02-Apr-15 APVD J. Broeksteeg 02-Apr-15		TE Connectivity			
DIMENSIONS: mm			TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 2 POS POWER CONNECTOR, WITH/ WITHOUT DETECTION CONTACTS PCB THICKNESS OF 1,6			
0 PLC $\pm 0,5$ 1 PLC $\pm 0,1$ 2 PLC $\pm 0,05$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES ± 2 FINISH			PRODUCT SPEC 108-19346 APPLICATION SPEC 114-19110 WEIGHT -		SIZE A2 CAGE CODE 00779 DRAWING NO C-1982295 RESTRICTED TO -			
Customer Drawing			SCALE 5:1		SHEET 1 OF 2		REV C1	

NOTES:

1. DURABILITY OF 1982295-4 CAN BE DECLARED ONLY AFTER TESTING.


2. TAIL LENGTH IS 3.6 MM FOR -6, OTHERS ARE 2.6 MM

3. OPTIONAL, THEY ARE REQUIRED WHEN CODING CONTACTS NEEDED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
IR	-		-	SEE SHEET 1	-	-	-


NOTES:

1. TRAY (PN 3178822-1) PACKAGING IS ONLY FOR PN 1982295-5.



DETAIL B

DO NOT SCALE



- NOTES:
- 1 MATERIAL: TRANSPARENT POLYSTYRENE ALLOY.
- 2 10 SPROCKET HOLES PITCH CUMULATIVE TOLERANCE +/-0,20.
- 3 CARRIER CAMBER IS WITHIN 1 mm IN 250 mm.
- 4 ALL DIMENSIONS MEET EIA-481-C REQUIREMENTS.
- 5 THICKNESS: 0,50±0,05mm.
- 6 REEL PACKAGING ONLY FOR OTHER PART NUMBERS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. Annokkee 02-Apr-15	TE Connectivity			
DIMENSIONS:		CHK R. Annokkee 02-Apr-15				
mm		APVD J. Broeksteeg 02-Apr-15	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	2 POS POWER CONNECTOR WITHOUT DETECTION CONTACTS PCB THICKNESS OF 1,6			
0 PLC ±0,5		108-19346	SIZE		DRAWING NO	
1 PLC ±0,1		APPLICATION SPEC	A2		100779	
2 PLC ±0,05		114-19110	CAGE CODE		C-1982295	
3 PLC ±		WEIGHT	-		RESTRICTED TO	
4 PLC ±		Customer Drawing	SCALE		5:1	
ANGLES ±2			SHEET		2 OF 2	
FINISH			REV		C1	