






.039	.230	.426	.534	.605	2.178	2.635	2.406	.441	2.079	78	1-2157480-5
[0.99]	[5.84]	[10.82]	[13.56]	[15.37]	[55.32]	[66.93]	[61.11]	[11.20]	[52.81]		
.039	.230	.426	.422	.494	2.272	2.729	2.500	.329	2.182	62	1-2157480-4
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[57.71]	[69.32]	[63.50]	[8.36]	[55.42]		
.039	.230	.426	.422	.494	1.625	2.088	1.852	.329	1.534	44	1-2157480-3
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[41.27]	[53.03]	[47.04]	[8.36]	[39.96]		
.030	.235	.422	.422	.494	1.083	1.541	1.132	.329	.994	26	1-2157480-2
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[27.51]	[39.14]	[28.75]	[8.36]	[25.25]		
.030	.235	.422	.422	.494	.759	1.213	.984	.329	.666	15	1-2157480-1
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[19.28]	[30.81]	[24.99]	[8.36]	[16.92]		
.039	.230	.426	.534	.605	2.178	2.635	2.406	.441	2.079	78	2157480-5
[0.99]	[5.84]	[10.82]	[13.56]	[15.37]	[55.32]	[66.93]	[61.11]	[11.20]	[52.81]		
.039	.230	.426	.422	.494	2.272	2.729	2.500	.329	2.182	62	2157480-4
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[57.71]	[69.32]	[63.50]	[8.36]	[55.42]		
.039	.230	.426	.422	.494	1.625	2.088	1.852	.329	1.534	44	2157480-3
[0.99]	[5.84]	[10.82]	[10.72]	[12.55]	[41.27]	[53.03]	[47.04]	[8.36]	[39.96]		
.030	.235	.422	.422	.494	1.083	1.541	1.132	.329	.994	26	2157480-2
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[27.51]	[39.14]	[28.75]	[8.36]	[25.25]		
.030	.235	.422	.422	.494	.759	1.213	.984	.329	.666	15	2157480-1
[0.76]	[5.97]	[10.72]	[10.72]	[12.55]	[19.28]	[30.81]	[24.99]	[8.36]	[16.92]		
DIM K	DIM J	DIM H	DIM G	DIM F	DIM E	DIM D	DIM C	DIM B	DIM A	NO. OF POSITIONS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG. C.C.THOMAS 10-14-14		 TE Connectivity					
						CHK. C.DERRICK 10-14-14							
						APPD. C.DERRICK 10-14-14							
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:				NAME		PLUG ASSY, SIZE 1-5, IP67 SERIES 109, AMPLITUDE WITH IF SEAL AND GROMMET					
INCHES [mm]		C.DERRICK											
		0 PLC ± —		PRODUCT SPEC		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		1 PLC ± —		APPLICATION SPEC									
		2 PLC ± —											
		3 PLC ± —											
4 PLC ± —		FINISH		WEIGHT		A1		00779		C=2157480		—	
ANGLES ± .1°													
MATERIAL SEE CALLOUTS		SEE CALLOUTS				CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1		REV C	