





H
G
F
E
D
C
B
A



Recommended PCB Layout

▨ Solder Area



Specifications 规格

Material 物料

Plastic Housing 塑胶外壳: Polyester, LCP, UL94V-0
Contact 接触: Copper Alloy

Plating 电镀

See Ordering Grid

Electrical 电气

Current Rating 电流额定值: 1 Amp
Contact Resistance 接触电阻值: 20 mΩ max.
Insulation Resistance 绝缘电阻值: 1000 MΩ min.
Dielectric Withstand Voltage 寒耐压: 300 V AC

Mechanical & Environmental 机械 & 环境


Operating Temperature 工作温度: -40°C to +105°C
Soldering Process 可焊性:

IR Reflow 回流焊: 260°C for 10 sec.
Wave 波峰焊: 250°C for 5-10 sec
Manual Solder 人工焊接: 350°C for 3-5 sec

Mates with (subject to pin length) 配套之母座 (在端子长度适合的条件下):

BC084 BC085

Ordering Grid



No. of Contacts
04 to 80

Contact Plating
A = Gold Flash All Over (Standard)
C = Tin All Over

Insulator Height 'H'
K = 1.00mm (Standard)
A = 1.50mm

Locating Peg
0 = No Peg
1 = With Peg

Dimension F (1/100mm) (Post Height)
0200 = 2.00mm (Standard)
0380 = 3.80mm (Standard)
or specify custom post height
eg. 0250 = 2.50mm

Packing Options

B = Tape & Reel with Cap (Standard)
D = Tube (Options D, E & G not available in 4-18 contacts)
E = Tube with Cap
G = Plastic Box

Insulator Material
L = LCP

Dimension E (1/100mm) (Footprint Width)
0480 = 4.80mm (Standard)
or specify custom footprint width
eg. 0250 = 2.50mm

Dimension D (1/100mm) (Top of Insulator to Bottom of Pin)
0160 = 1.60mm (Standard)
or specify custom length
eg. 0250 = 2.50mm

Number of Contacts	Dimensions		
	A	B	C
4	1.00	2.00	---
6	2.00	3.00	---
8	3.00	4.00	---
10	4.00	5.00	3.00
12	5.00	6.00	4.00
14	6.00	7.00	5.00
16	7.00	8.00	6.00
18	8.00	9.00	7.00
20	9.00	10.00	8.00
22	10.00	11.00	9.00
24	11.00	12.00	10.00
26	12.00	13.00	11.00
28	13.00	14.00	12.00
30	14.00	15.00	13.00
32	15.00	16.00	14.00
34	16.00	17.00	15.00
36	17.00	18.00	16.00
38	17.00	18.00	17.00
40	19.00	20.00	18.00
42	20.00	21.00	19.00
44	21.00	22.00	20.00
46	22.00	23.00	21.00
48	23.00	24.00	22.00
50	24.00	25.00	23.00
52	25.00	26.00	24.00
54	26.00	27.00	25.00
56	27.00	28.00	26.00
58	28.00	29.00	27.00
60	29.00	30.00	28.00
62	30.00	31.00	29.00
64	31.00	32.00	30.00
66	32.00	33.00	31.00
68	33.00	34.00	32.00
70	34.00	35.00	33.00
72	35.00	36.00	34.00
74	36.00	37.00	35.00
76	37.00	38.00	36.00
78	38.00	39.00	37.00
80	39.00	40.00	38.00

Part Number BC050		Product Description 1.0mm Pitch Pin Header, Dual Row, Surface Mount, Vertical	
Drawing Date 20th May 2008			
By ASE	Packing Clarification F	Tolerances (Except as Noted) Length: X. ± 0.30 X.X ± 0.25 X.XX ± 0.15 X.XXX ± 0.10	Angle: X° ± 5° X.X° ± 3° X.XX° ± 2° X.XXX° ± 1°
Revision Date	05/01/10	Units: Metric (mm)	3rd Angle Projection
<p>This drawing is confidential and copyright of Global Connector Technology, Ltd (GCT). This drawing must not be copied or disclosed without written consent. E & OE</p>			

GCT
Global Connector Technology
www.gct.co

Not to Scale	Drawn By ASE	Sheet No. 1/1
--------------	-----------------	------------------