

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

170071-4011

Status:


Active

Overview:

High-Speed Pluggable I/O Solutions

Description:

zSFP+™ Stacked Ganged Assembly with Elastomeric Gasket, 2-by-4 with 4 Light Pipes, 160 Circuits



Documents:

3D Model

Drawing (PDF)

Application Specification AS-170071-0001 (PDF)

Test Summary TS-170071-0001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	I/O Connectors
Series	170071
Application	Module-to-Board
Component Type	Receptacle
Electrical Model	Yes
Overview	High-Speed Pluggable I/O Solutions
Product Name	zSFP+™
Type	N/A
UPC	884982402195
Physical	
Circuits (Loaded)	160
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Gender	Female
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	98.604/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.36mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	8
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series	
170071Series	
Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Stacked Multi-Port Extraction Tool, 2 by 4	0622029940
2-by-4 SFP Stacked Multi-Port Insertion Tool	0622030150

Current - Maximum per Contact	0.5A
Shield Type	N/A
Shielded	Yes
Voltage - Maximum	30V AC

Material Info

Reference - Drawing Numbers

Application Specification	AS-170071-0001
Electrical Model Document	EE-170071-0001
S-Parameter Model	SP-170071-0001
Sales Drawing	SD-170071-0002
Symbol/Footprint Data	SYM-170071-0001
Test Summary	TS-170071-0001

This document was generated on 04/28/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION