



DEBUR AND BREAK SHARP EDGES

DO NOT SCALE DRAWING

REVISION



THREAD	KIT QTY	L	D	H	s	t
M3	50.0	8.0	5.5	3.0	2.5	1.3
M3	50.0	10.0	5.5	3.0	2.5	1.3
M3	50.0	16.0	5.5	3.0	2.5	1.3
M4	25.0	10.0	7.0	4.0	3.0	2.0
M4	20.0	16.0	7.0	4.0	3.0	2.0
M4	20.0	20.0	7.0	4.0	3.0	2.0
M4	10.0	30.0	7.0	4.0	3.0	2.0
M5	15.0	10.0	8.5	5.0	4.0	2.5
M5	15.0	16.0	8.5	5.0	4.0	2.5
M5	15.0	20.0	8.5	5.0	4.0	2.5
M5	15.0	30.0	8.5	5.0	4.0	2.5
M6	20.0	10.0	10.0	6.0	5.0	3.0
M6	20.0	16.0	10.0	6.0	5.0	3.0
M6	20.0	20.0	10.0	6.0	5.0	3.0
M6	20.0	25.0	10.0	6.0	5.0	3.0
M8	10.0	16.0	13.0	8.0	6.0	4.0
M8	10.0	20.0	13.0	8.0	6.0	4.0
M8	10.0	30.0	13.0	8.0	6.0	4.0
M8	10.0	40.0	13.0	8.0	6.0	4.0
M8	10.0	50.0	13.0	8.0	6.0	4.0

A

DRAWN 06/07/15

NOTES

DIN 912



DESIGN RIGHT. TR FASTENINGS LTD, 2003  
 UNDER NO CIRCUMSTANCES MUST THIS  
 DRAWING BE COPIED OR DISCLOSED,  
 WITHOUT FIRST OBTAINING WRITTEN  
 AUTHORITY.

UNLESS OTHERWISE SPECIFIED:  
 DIMENSIONS ARE IN MILLIMETERS  
 SURFACE FINISH:  
 TOLERANCES:

ISO 2768 m

NAME	DATE
DRAWN MARTIN ELLIOTT	06/07/15
CHK'D	
APPVD	

CUSTOMER PART No

MATERIAL:

STEEL

HEAT TREATMENT

GRADE 12.9

FINISH:

ZINC PLATED

TITLE:


SOCKET CAP SCREW KIT

DWG NO.

TRFAKIT0012

A3

PROJECTION



SHEET 1 OF 1