


LOC		DIST		REVISIONS					
G	14	P	LTR	DESCRIPTION			DATE	DWN	APVD
			D3	REVISED PER ECO-15-007953			28MAY2015	NK	DR


 WIRE RANGE	 E13288 Listed	 LR7189 Certified
16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED	16-14 AWG SOLID OR STRANDED



- 1
- STAMP AMP 16-14* APPROX AS SHOWN.
- 2
- WIRE INSULATION DIA: .105-.150.
- 3
- TONGUE MATERIAL THK: .031±.002.
- 4
- BODY & SLEEVE: CU PER ASTM B152
BODY & SLEEVE: TIN PLATE .000100 MIN
EXT THK PER ASTM B545
INSULATION: NYLON PER ASTM D4066
COLOR - BLUE.
- 5
- APPLIES FROM EDGE OF METAL WIRE BARREL
TO CENTER OF STUD HOLE.
- 6
- MEETS MS25036-152, CLASS 1 & 2.

100	LOOSE PIECE, BOX	4	8-324159-1
5000	324159 ON TAPE & REEL	4	2-324159-2
---	LOOSE PIECE	4	324159
QTY	PACKAGE TYPE	MATERIAL FINISH	PART NO

CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 300 V MAX
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED OR SOLID
FOR ORDER ENTRY	1-800-526-5142	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -
MATERIAL SEE TABLE	FINISH SEE TABLE

DWN JR RUTH	13JAN10	 TE Connectivity			
CHK T MICHIELUTTI	13JAN10	NAME TERMINAL, RING TONGUE, PIDG WIRE SIZE: 16-14 AWG			
APVD T MICHIELUTTI	13JAN10	SIZE A3			
PRODUCT SPEC ---		CAGE CODE 00779			
APPLICATION SPEC ---		DRAWING NO C-324159			
WEIGHT ---		RESTRICTED TO ---			
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1	REV D3	