




FEMALE END VIEW

3 4 1 2

euro fast.




SPECIFICATIONS	
CONTACT MATERIAL/PLATING	BRASS/GOLD
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
MAXIMUM WIRE SIZE	18 AWG
CABLE GRIP RANGE	6–8mm
TEMPERATURE RATING	–40°C to +85°C (–40°F to +185°F)
PROTECTION CLASS	IEC IP67
WIRE TERMINATION	SCREW TERMINAL



SOURCE DRAWING – FOR REFERENCE ONLY

ALL METAL SHIELDED FIELD WIREABLE CONNECTOR

ALL METAL SHIELDED FIELD WIREABLE CONNECTOR					RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com	
					1. 2. 3. 4.				TURCK INC <i>High Technology Sensors and Automation Controls</i>			
					MATERIAL							
					SEE SPECIFICATIONS							
FINISH		ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR REFERENCE ONLY		DRFT GJA		DATE 09/07/01		DESCRIPTION CMB 8141-0				
SEE SPECIFICATIONS				APVD		SCALE 1=1.0						
				CONTACT TURCK FOR MORE INFORMATION		UNIT OF MEASUREMENT MILLIMETER [INCH]		IDENTIFICATION NO. U6112-01		REV B		
B	REMOVE PROTRUDING PIECE AND SLEEVE	TV	07/13/15	50500			DO NOT SCALE THIS DRAWING		FILE: U6112-01		SHEET 1 OF 1	
REV	DESCRIPTION	BY	DATE	ECO NO.								