


SPECIFICATIONS						
CONTACT CARRIER MATERIAL	NYLON OR TPU					
MOLDED HEAD MATERIAL/COLOR	TPU/YELLOW					
CONTACT MATERIAL/PLATING	BRASS/GOLD					
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL					
RATED CURRENT [A]	4.0 A					
RATED VOLTAGE [V]	125 VAC/VDC					
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW					
CONDUCTOR INSULATION MATERIAL	PVC					
NUMBER OF CONDUCTORS [AWG]	3x24 AWG					
TEMPERATURE RATING	-40°C TO +105°C (-40°F TO +221°F)					
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67					



CABLE LENGTH	TOLERANCE *			
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER			
STRIP LENGTH	TOLERANCE *			
0-7mm	±0.5mm			
8-29mm	±1.0mm			
30-49mm	±2.0mm			
50-69mm	±3.0mm			
70-100mm	±4.0mm			
OVER 100mm	±5.0mm			
* UNILESS OTHERWISE SPECIFIED				

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

					ľ
D	UPDATE MALE COUPLING NUT PER ECO	KMY	05/09/13	40191	
REV	DESCRIPTION	BY	DATE	ECO NO.	

SOURCE DRAWING - FOR REFERENCE ONLY

RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology	RCK Inc	3000 CAMPUS MINNEAPOLIS, MN 1-800-544-7 (763) 553-7 (763) 553-0 turck.com	1 55441 7769 300 708 fax
MATERIAL	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR	APVD	DATE 07/22/04 SCALE 1=1.0	PKG 3M-*-	PSG 3M	
FINISH	REFERENCE ONLY CONTACT TURCK FOR MORE INFORMATION	UNIT OF ME		IDENTIFICATION NO.		rev D
		DO NOT SCALE	THIS DRAWING	FILE: 777000431	SHEET	1 OF 1