






REVERSED OUTER
1-2288172-8, 2-2288172-0
SCALE 4:1



TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

173.5	EMI SPRINGS	REVERSED OUTER	2-2288172-0
		CENTER/REVERSED OUTER	1-2288172-9
176.25	EMI GASKET	REVERSED OUTER	1-2288172-8
		CENTER/REVERSED OUTER	1-2288172-7
173.5	EMI SPRINGS	OUTER	2288172-8
		INNER	2288172-7
		INNER/OUTER	2288172-6
		NONE	2288172-5
176.25	EMI GASKET	OUTER	2288172-4
		INNER	2288172-3
		INNER/OUTER	2288172-2
		NONE	2288172-1
(E)	CAGE TYPE	LIGHT PIPE CONFIGURATION	PART NUMBER

4805 (3/11)







2288172-7
EMI SPRINGS ONLY
SCALE 3:1



DESIGN APPROVED THIS PRINT IS
PRELIMINARY
TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M. SHIRK 26JAN2015	TE Connectivity	
DIMENSIONS: mm		CHK P. RECCE 26JAN2015		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD -	NAME	
0 PLC ±0.10		PRODUCT SPEC	RECEPTACLE ASSEMBLY, 2X12, STACKED, zSFP+	
1 PLC ±0.10		108-2431		
2 PLC ±0.10		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO	
3 PLC ±0.10		114-13319	A100779C=2288172	
4 PLC ±		WEIGHT	RESTRICTED TO	
ANGLES FINISH		CUSTOMER DRAWING	SCALE 2:1 SHEET 2 OF 5 REV 1	

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-






DETAIL G
12X INDIVIDUALLY
STACKED, zSFP+
SCALE 10:1

DESIGN APPROVED THIS PRINT IS
PRELIMINARY
TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009				DWN M. SHIRK 26JAN2015	 TE Connectivity			
DIMENSIONS: mm				CHK P. RECCE 26JAN2015				
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APVD -	NAME RECEPTACLE ASSEMBLY, 2X12, STACKED, zSFP+			
				PRODUCT SPEC 108-2431				
				APPLICATION SPEC 114-13319	SIZE A100779			
MATERIAL SEE NOTES		FINISH -		WEIGHT -		DRAWING NO C=2288172		RESTRICTED TO -
CUSTOMER DRAWING				SCALE 2:1		SHEET 3		OF 5
						REV 1		

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
				-	-	SEE SHEET 1	-	-	-




RECOMMENDED PCB LAYOUT
SCALE 3:1





DESIGN APPROVED THIS PRINT IS
PRELIMINARY
TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN M. SHIRK CHK P. RECCE APVD -	26JAN2015 26JAN2015 -	TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, 2X12, STACKED, zSFP+	
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		±0.10 ±0.10 ±0.10 ±0.10 ± ±		PRODUCT SPEC 108-2431 APPLICATION SPEC 114-13319	
MATERIAL SEE NOTES		WEIGHT -		SIZE A100779C=2288172	
		CUSTOMER DRAWING		RESTRICTED TO -	
		SCALE 2:1		SHEET 4 OF 5	
				REV 1	


LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-	-	SEE SHEET 1	-	-	-




DETAIL C
RECOMMENDED PIN AND LIGHT PIPE LAYOUT
SCALE 10:1



DETAIL D
PIN MAP
12 PLACES
SCALE 20:1



RECOMMENDED BEZEL CUT OUT DETAIL



RECOMMENDED BEZEL LOCATION WITH EMI GASKET
SCALE 3:1

DESIGN APPROVED THIS PRINT IS
PRELIMINARY
TO FIRST PIECE APPROVAL
CONTACT PRODUCT ENGINEERING
BEFORE USING THIS PRINT

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009		DWN M. SHIRK CHK P. RECCE APVD	26JAN2015 26JAN2015	NAME	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	
0 PLC ±0.10 1 PLC ±0.10 2 PLC ±0.10 3 PLC ±0.10 4 PLC ±0.10		±0.10 ±0.10 ±0.10 ±0.10 ±0.10		108-2431	
ANGLES FINISH		±0.10 ±0.10		APPLICATION SPEC	
MATERIAL		114-13319		SIZE	
SEE NOTES		WEIGHT		A100779	
SEE NOTES		CUSTOMER DRAWING		C=2288172	
SCALE		2:1		SHEET	
5		OF		5	
REV		1		RESTRICTED TO	