




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		P2	REVISED PER ECO-15-005911	20MAY15	KG	DM



1. THIS RCPT. IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 2. MAX WIRE INSUL TO BE USED WITH THIS RCPT IS .068 DIA
 3. STAINLESS STEEL RETENTION CLIPS ARE INCLUDED IN INSERTS
 4. PACKAGE STAMPED M24308/2-281F
 5. THIS RCPT. WILL ACCEPT SIZE 20 SOCKET CONTACT M39029/63-368 OR ANY AMP HD-20 SOCKET CONTACT
- △6 AMP PART NO. STAMPED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- △7 UL/CSA DESIGNATION STAMPED IN THIS AREA.
- △8 RESTRICTED ITAR DRAWING.
- △9 FINISH: PLATED BRIGHT TIN .000400 MIN THK PER ASTM-B-545 OVER COPPER PLATE .000050 MIN THK PER MIL-C-14550.



SUPSC BY 205161-1	△9	STEEL, CLASS G	205161-5
	-	-	205161-4
SUPSD BY 207253-2	CADMIUM PER QQ-P-416	STEEL, CLASS G	205161-3
	CADMIUM PER QQ-P-416	BRASS	205161-2
	CADMIUM PER QQ-P-416	STEEL, CLASS G	205161-1
	SHELL FINISH	SHELL MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	1-12-05	TE TE Connectivity			
DIMENSIONS: INCHES		CHK	1-12-05				
		APVD	1-12-05	NAME			
		PRODUCT SPEC					
MATERIAL		APPLICATION SPEC		RCPT ASSY,AMPLIMITE, SIZE 1,9 POSN,SERIES 109			
SEE CALLOUTS		WEIGHT	-				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CUSTOMER DRAWING		SCALE	4:1	SHEET	1 of 1
FINISH						REV	P2