

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AG	00		F2	REVISED PER ECO-11-004820	11MAR11	RK	HMR

D

C

B



A

D


C

B


A



SEE DETAIL A



DETAIL A
SCALE 10:1



SECTION B-B
SCALE 10:1

- 1 MATERIAL:
HOUSING: GLASS-FILLED POLYESTER, COLOR-BLACK.
CONTACT: BERYLLIUM COPPER.
- 2 CONTACT PLATED WITH 0.00254 [.000100] TIN-LEAD OVER ALL.
- 3 CONTACT PLATED WITH 0.00038 [.000015] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVER ALL.
- 4 CONTACT PLATED WITH 0.00076 [.000030] GOLD IN CONTACT AREA OVER 0.00127 [.000050] NICKEL OVER ALL.
- 5 PART NO. DENOTES INDIVIDUAL TWO POSITION SHUNT, WHICH IS PACKAGED ON BREAKAWAY COMBS OF TEN SHUNTS.
6. CONNECTOR MATES WITH WIRE WRAP POSTS, 0.64 [.025] SQUARE OR ROUND AND 0.56 [.022] X 0.66 [.026] POSTS. LENGTH 5.08 [.200] MINIMUM.
- 7 CONTACT PLATED WITH 0.00254 [.000100] MATTE TIN OVER ALL.
- 8 PART NO. DENOTES INDIVIDUAL TWO POSITION SHUNT, WHICH IS PACKAGED LOOSE PIECE.
- 9 PRELIMINARY P/N - NOT RELEASED FOR PRODUCTION

OBSOLETE				
	7	7	8	531230-5
				531230-4
	4			531230-3
		3		531230-2
			2	531230-1
			FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R.TALLEY	3-12-91	 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK —	—	NAME LOW PROFILE SHUNT CONNECTOR 5.08 [.200] CL —			
		APVD —	—				
		PRODUCT SPEC 108-9057					
		APPLICATION SPEC 114-1059					
MATERIAL 		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C-531230	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 of 1	REV F2	