

SAFETY ORGANIZATIONS

THE CONNECTOR USED IN THIS ASSEMBLY HAS RECEIVED RECOGNITION, CERTIFICATION AND APPROVAL IN FILES INDICATED BY THE FOLLOWING AGENCIES:

UL: E29179
CSA: LR19980
TUV: R9151436

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 15 AMP, 125 VDC,

LINE FREQUENCY: N/A

MAXIMUM LEAKAGE CURRENT, N/A
EACH LINE TO GROUND:

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, I_r .

IN AN AMBIENT, T_o , HIGHER THAN 55°C, THE MAXIMUM OPERATING CURRENT, I_o , IS AS FOLLOWS:

$$I_o = I_r \sqrt{\frac{100 - T_o}{45}}$$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C
HUMIDITY: 21 DAYS @ 40°C 95% RH.
CURRENT OVERLOAD TEST: 6 TIMES I_r FOR 8 SECONDS

TEST SPECIFICATIONS:

INDUCTANCE: XXXX mH NOMINAL
CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)
LINE TO GROUND: X.XXXX μ F ±20%
LINE TO LINE: X.XXXX μ F ±20%
DISCHARGE RESISTOR: X.XM Ω
L/G AND L/L I.R.:
NO DISCHARGE RESISTOR: 6000M Ω (MIN.) @ 100VDC, 20°C AND 50% RH



FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.

CUSTOMER DRAWING

CATALOG # GA310

ECN #	APPRVD.	DATE



50 Ω - 50 Ω (MINIMUM) INSERTION LOSS

FREQUENCY MHz	/	/	/	/	/	/	/	/	/	/	/
COMMON dB	/	/	/	/	/	/	/	/	/	/	/
DIFF. dB	/	/	/	/	/	/	/	/	/	/	/

THIRD ANGLE
PROJECTION



UNLESS OTHERWISE SPECIFIED,
TOLERANCE TO BE ±.025
MATERIAL & FINISH: AS SUPPLIED

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO
TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES
AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN
TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION
FROM TYCO ELECTRONICS CORPORATION.
HARRISBURG, PENNSYLVANIA USA



Tyco Electronics

CORCON PRODUCTS, 620 S. BUTTERFIELD RD. MUNDELEIN IL 60060

CONNECTOR ASSEMBLY

TYCO ELECTRONICS PART NO.		0-1609136-2	
SCALE:	NTS	DATE:	30MAR04
DRW. BY:	SD	ORIG:	ELC
CATALOG NO.		GA310	
REV.		0	