




1

.000100-.000200 BRIGHT TIN-LEAD OVER .000030 NICKEL ENTIRE CONTACT

2

.000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

3

.000030 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN-LEAD IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT

4

POINT OF MEASUREMENT FOR PLATING THICKNESS

5

GOLD PLATING NOT REQUIRED IN THIS AREA

6

.000100-.000200 BRIGHT TIN OVER .000030 NICKEL ENTIRE CONTACT.

7

.000015 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

8

.000030 GOLD IN CONTACT AREA, .000050-.000100 BRIGHT TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

9

.000100-.000200 MATTE TIN OVER .000030 NICKEL ENTIRE CONTACT.

10

.000015 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

11

.000030 GOLD IN CONTACT AREA, .000050-.000100 MATTE TIN IN CRIMP AREA, ALL OVER .000030 NICKEL ENTIRE CONTACT.

11	5-104505-7	5-104505-6
10	5-104505-5	5-104505-4
9	5-104505-3	5-104505-2
8	1-104505-3	1-104505-2
7	1-104505-1	1-104505-0
6	104505-9	104505-8
3	104505-7	104505-6
2	104505-5	104505-4
1	104505-3	104505-2
FINISH	LOOSE PIECE PART NUMBER	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D KEITZER 12-14-88	TE Connectivity	
DIMENSIONS: INCHES		CHK S. SHUEY 12-15-88		
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
	0 PLC ± -		APVD C.SINISI 12-16-88	
	1 PLC ± -		PRODUCT SPEC	
	2 PLC ± -		APPLICATION SPEC	
3 PLC ± .005		—		
4 PLC ± -		—		
ANGLES ± -		WEIGHT		
FINISH		—		
MATERIAL PHOS BRONZE		SEE TABLE		
CUSTOMER DRAWING		SCALE 10:1		
SHEET 1 of 1		REV F1		