

MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91 929



SWITCH-BASIC

CATALOG LISTING

V7-2B17D8-048

CW-B3088

CATALOG LISTING
V7-2B17D8-048
REPLACES
RELEASE NO. PR-19143
ISSUE
M
2




NOTE
1 - CAUTION: OVERTRAVEL FORCE ON LEVER MUST NOT RESULT IN AN OVERTRAVEL FORCE ON PLUNGER EXCEEDING 5 LBS

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE --- 20 GRAMS MAX	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ± WEIGHT	
RELEASE FORCE --- 1 GRAM MIN	L156 11A 1/3HP 125, 250 OR 277 VAC 1/2A 125 VDC, 1/4A 250 VDC 4A 125 VAC "L"		
DIFFERENTIAL TRAVEL --- .050 MAX			
OVERTRAVEL --- .115 MIN			
RELEASE TRAVEL --- .030 MIN			



REVISIONS
A CO 76214
G R T
20 OCT 93

DDM/CAD
DRAWN
B A B 20 JUN 91
CHECK
L A D 26 JUN 91
CHECK