ECN# APP'D./DATE 10419 TAM 6/6/94 10 SAFETY ORGANIZATION(5): THIS MODULE HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS RELIABILITY SPECIFICATIONS:

HAVE BEEN MET UL RECOGNIZED

UI 498

CSA CERTIFIED

CSA 22.2, NO.0, 0.4, 42

VDE APPROVED

VDE 625

OPERATING SPECIFICATIONS:

6 AMP, 120 VAC 6 AMP./40°C, 250 VAC LINE VOLTAGE/CURRENT.

LINE FREQUENCY: 47-440Hz

STORAGE TEMPERATURE: -55°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH CURRENT OVERLOAD TEST: 6 TIMES RATED CURRENT FOR 8 SECONDS

TEST SPECIFICATIONS:

LINE/GROUND AND LINE/LINE INSULATION RESISTANCE.

6000MΩ (MIN) AT 100VDC 20°C AND 50% RH


RECOMMENDED RECEIVING INSPECTION HIPOT:

LINES TO GROUND: LINE TO LINE

1500 VAC FOR 1 MINUTE 1450 VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



UNLESS OTHERWISE SPECIFIED, TOLERANCE TO BE ±.025

MATERIAL & FINISH: AS SUPPLIED

This document is proprietary to CORCOM INC. and is not to be reproduced nor used for manufacturing purposes except on CORCOM'S prior written consent.



POWER LINE FILTER

APPRVD.

DATE: 4-18-94 CATALOG NO.

10 6VM4.

CAD NO. 6VM4.10