



Aug.1.2016 Copyright 2016 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

TO

A
B
C
D
E
F



COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				. .	△				. .
△				. .	△				. .
△				. .	△				. .



NOTES 1. PER REEL:10000 CONTACTS.
2. APPLICABLE CABLE
CABLE SIZE:28AWG(7/0.127) AND 30AWG(7/0.10)
OUTER DIAMETER:φ0.5 TO 0.6mm.

1		PHOSPHOR BRONZE		CONTACT AREA:GOLD PLATED 0.1μ m min OUTSIDE OF BARREL:TIN PLATED 1μ m min OTHERS:NICKEL PLATED 0.5μ m min			
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	
CODE NO.(OLD)		DRAWN		DESIGNED		CHECKED	
		A.Miura		T.Kumagawa		H.Umehara	
		'07. 04.04		'07.04.05		'07.04.05	
						T.Oma	
						'07. 04.06	
SCALE 20:1		DRAWING NO. EDC3-302549-01		PART NO. DF19A-2830SCFA			
UNITS mm		HRS HIROSE ELECTRIC CO.,LTD.		CODE NO. CL685-0048-6		1/1	

A
B
C
D
E
F