





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION, 19
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.





- 1 GOLD PLATING NOT REQUIRED IN THIS AREA.
- 2 LOOSE PIECE CUT-OFF DIMENSION.
- 3 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BEAMS)
- 4 .00030 GOLD IN CONTACT AREA, GOLD FLASH ON REMAINDER OF TERMINAL, ALL OVER .00050 NICKEL.
- 5 .00010+.000200 BRIGHT TIN-LEAD OVER .00050 NICKEL.
- 6 POINT OF MEASUREMENT FOR PLATING THICKNESS (INSIDE BARREL)
- 7 OBSOLETE PART NO.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
0	✓	0		RELEASED	
01	✓	01		REV PER ECN 708	WBL 6-24-88
02	✓	02		REV ECN 980	Hm 3-24-88
03	✓	03		REV ECN AR2029	DK 9-28-88
04	✓	04		REV ECN AR2149	DK 10-31-88
05	✓	05		REV LOC & DIST AD-4171	11-27-89
06	✓	06		REV PER AD-5350	2-10-91
07	✓	07		OBS -4 PER 0010-0976-93	1-13-93
08	✓	08		REV PER 0010-0312-96	1-21-97



SECT. B-B

SECT. C-C
WIRE SIZE: #27-#32SECT. D-D
INSULATION RANGE:
.040/.020

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ±	CONTRACT NO. DR CHK APPD DSGN APPD OTHER APPD	NAME CONTACT, MOD II, CRIMP SNAP-IN, STRIP
MATERIAL PHOS. BRONZE, .008 THICK.	FINISH SEE TABLE	SIZE C
FSCM NO. 00779		DRAWING NO. 103455
SCALE 10:1		SHEET 1 OF 1

CUSTOMER DRAWING