









PROTECTIVE SIDES AVAILABLE ON ALL CIRCUITS EXCEPT TWO AND FOUR CIRCUITS.



PROTECTIVE SIDES AVAILABLE ON ALL CIRCUITS EXCEPT TWO AND FOUR CIRCUITS.



NOTES:

1. MATERIAL: UNFILLED POLYESTER. U.L. 94V-0. HOUSING COLOR: SEE CHART
2. FINISH: N/A
3. PRODUCT SPECIFICATION: PS-5556-003
4. PACKAGING SPECIFICATION: PK-30067-001.
5. HOUSING TO BE USED WITH TERMINAL #5556. AND T.P.A. LOCK #30072-*. RECEPTACLE HOUSING TO MATE WITH PLUG HOUSING #30068, ST. HEADER #30069, AND RT. ANGLE HEADERS #30070 & #44483. HOUSING ACCEPTS CONNECTOR POSITIONING ASSURANCE (C.P.A.) LOCK #30071.
6. RELIEF NOTCH IS OPTIONAL AND MAY OR MAY NOT APPEAR ON 2, 4, 6, 10 & 12 CIRCUIT HOUSINGS ONLY.
7. FOR 2 CKT HOUSING, DIMENSION IS .231/5.88
8. FOR 2 & 4 CKT HOUSINGS, DIMENSION IS .070/1.78
9. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPEC PS-45499-002.
10. CHAMFERS ARE OPTIONAL AND MAY OR MAY NOT BE PRESENT ON 16 CIRCUIT HOUSINGS.
11. TEXT ON PART IS FOR REFERENCE ONLY. TEXT AND TEXT LOCATION MAY VARY DEPENDING ON PART NUMBER AND/OR TOOL.

ADD 10, 12 CKT VIEW EC NO: UCP2016-4837 DRWN:SLAFTER 2016/06/21 CHKD:JBELL 2016/06/21 APPR:FSMITH 2016/06/28	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table><tr><td></td><td>mm</td><td>INCH</td></tr><tr><td>4 PLACES</td><td>± .005</td><td>± .005</td></tr><tr><td>3 PLACES</td><td>± .005</td><td>± .010</td></tr><tr><td>2 PLACES</td><td>± .025</td><td>± .014</td></tr><tr><td>1 PLACE</td><td>± .036</td><td>± .014</td></tr><tr><td>0 PLACE</td><td>± .036</td><td>± .014</td></tr></table> ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		mm	INCH	4 PLACES	± .005	± .005	3 PLACES	± .005	± .010	2 PLACES	± .025	± .014	1 PLACE	± .036	± .014	0 PLACE	± .036	± .014	DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
					mm	INCH																					
				4 PLACES	± .005	± .005																					
				3 PLACES	± .005	± .010																					
				2 PLACES	± .025	± .014																					
				1 PLACE	± .036	± .014																					
0 PLACE	± .036	± .014																									
DRAWN BY R/JF		DATE 09/23/91	TITLE 2-16 CKT. RECPT. HSG. MINI-FIT T.P.A. SERIES																								
CHECKED BY GEP		DATE 09/23/91	molex																								
APPROVED BY FSMITH		DATE 2010/10/25	SEE CHART																								
MATERIAL NO.		DOCUMENT NO.			SHEET NO. 1 OF 2																						
SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									

	13	12	11	10	9	8	7	6	5	4	3	2	1	
J	BLACK		NATURAL											J
	CKT. SIZE	ENG. NO.	EDP. NO.	ENG. NO.	EDP. NO.	DIM. "A"	DIM. "B"							
	02	30067-02A2	I5-97-502 I	30067-02 12	30067-0212	—	.467 (11.86)							
	04	30067-04A2	I5-97-504 I	30067-04 12	30067-0412	.165 (4.20)	.467 (11.86)							
I	06	30067-06A2	I5-97-506 I	30067-06 12	30067-0612	.331 (8.40)	.633 (16.08)							
	08	30067-08A2	I5-97-508 I	30067-08 12	30067-0812	.496 (12.60)	.798 (20.27)							
	10	30067-10A2	I5-97-510 I	30067-10 12	30067-1012	.661 (16.80)	.963 (24.46)							
H	12	30067-12A2	I5-97-512 I	30067-12 12	30067-1212	.827 (21.00)	1.129 (28.68)							
	14	30067-14A2	NOT TOOLED	30067-14 12	NOT TOOLED	.992 (25.20)	1.294 (32.87)							
	16	30067-16A2	I5-97-516 I	30067-16 12	30067-1612	1.157 (29.40)	1.459 (37.06)							
G														G
F														F
E														E
D														D
C														C
B														B
A														A
	12	11	10	9	8	7	6	5	4	3	2	1		

LEGEND:

30067 - ** * 2

CIRCUIT SIZE (02-16)

HOUSING COLOR
A = BLACK
1 = NATURAL

16 CIRCUITS

12 CKT.

10 CKT.

SEE NOTE 10

SEE SHEET 1 EC NO: UCP2016-4837 DRWNC:SLAFER 2016/06/21 CHKD:JBELL 2016/06/21 APPR:FSMITH 2016/06/28	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
	▽=0	mm INCH	IN/MM	2:1	METRIC	
	▽=0	4 PLACES ± --- ± ---	DRAWN BY DATE	2-16 CKT. RECPT. HSG. MINI-FIT T.P.A. SERIES		
	▽=0	3 PLACES ± --- ± .010	CHECKED BY DATE			
	REV	DESCRIPTION	2 PLACES ± 0.25 ± .014	GE P 09/23/91	molex	
		1 PLACE ± 0.36 ± ---	APPROVED BY DATE			
		0 PLACE ± ±	FSMITH 2010/10/25	SD-30067-*		
		ANGULAR ±1/2°	MATERIAL NO.			
H3		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE CHART	2 OF 2		
			SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION			

LEGEND:




30067 - ** * 2

CIRCUIT SIZE (02-16)

HOUSING COLOR

A = BLACK

1 = NATURAL



SEE SHEET 1 EC NO: UCP2016-4837 DRWNG:CLAFER CHKD:JBELL APPR:FSMITH 2016/06/21 2016/06/28	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION				
					IN/MM		2:1	METRIC	2-16 CKT. RECPT. HSG. MINI-FIT T.P.A. SERIES molex				
			4 PLACES	± .005	± .005	DRAWN BY	DATE	TITLE					
			3 PLACES	± .005	± .010	CHECKED BY	DATE						
			2 PLACES	± 0.25	± .014	GEP	09/23/91						
					1 PLACE	± 0.36	± .020	APPROVED BY			DATE	DOCUMENT NO.	
					0 PLACE	± .005	± .005	FSMITH			2010/10/25		
					ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-30067-*		2 OF 2		
							SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				