



- NOTES
- 1 CONTACT AREA:GOLD PLATING 0.2μm min.
LEAD AREA:GOLD PLATING FLASH.
UNDER PLATING:NICKEL 2μm min.
 - 2 THE RECOMMENDED CLAMP TORQUE OF REF.NO.□ TO BE 0.8N·m.
LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT
REF.NO.□ FROM LOOSENING.
 - 3 AFTER REF.NO.□ IS INSERTED TO REF.NO.□, REF.NO.□ IS MOUNTED ON THE PANEL.
MAKE SURE THAT REF.NO.□ DOES NOT HAVE ANY FACTORS TO REDUCE WATER-RESISTANCY,
SUCH AS SCRATCH, TWIST, PINCHING, OR DUST.

4	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0			
3	COPPER ALLOY	1	7	BRASS	NICKEL PLATING
2	COPPER ALLOY	1	6	PHOSPHOR BRONZE	NICKEL PLATING
1	POLYPHENYLENE SULFIDE	(BLACK) UL94V-0	5	CHLOROPRENE RUBBER	(BLACK)
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 5 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-000585	DESIGNED TP. KOMATSU
HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH	07. 03. 05	DRAWING NO.	EDC3-113453-71
		CHECKED : EJ. KUNII	07. 03. 05	PART NO.	HR30-7R-12P(71)
		DESIGNED : HS. KAWASHIMA	07. 03. 05	CODE NO.	CL130-1016-6-71
		DRAWN : MK. SATO	07. 03. 05		
				DATE	07. 07. 27