




- NOTES
- 1 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑥ TO BE 5 TO 5.5 N · m.
 - 2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑩ TO BE 0.2 TO 0.25 N · m.
 - 3 ROTATION EXAMPLES OF REF. NO. ① AND ⑥ ARE SHOWN.
 - 4 SCREW OF REF. NO. ①, ⑥, ⑧, LOCTITE 271, OR EQUIVALENT, LOCTITE JAPAN IS RECOMMENDED TO PREVENT FROM LOOSENING.
 - 5 THIS PRODUCT TO BE USED WITH CABLECLAMP, JR25WCC-**.
** DESIGNATE DIAMETER OF APPLICABLE CABLE.

5	PHOSPHOR BRONZE	NICKEL PLATING	10	STAINLESS STEEL	
4	PHENOL-FORMALDEHYDE	(BLACK) UL94V-0	9	NBR	(GRAY)
3	PHENOL-FORMALDEHYDE	(BLACK) UL94V-0	8	NBR	(GRAY)
2	COPPER ALLOY	SILVER PLATING 3 μm min.	7	BRASS	BLACK CHROME PLATING
1	ALUMINUM ALLOY	BLACK CHROME PLATING	6	BRASS	BLACK CHROME PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
		APPROVED : SU. OBARA 09.09.30		DRAWING NO. EDC3-110546-71			
HIROSE ELECTRIC CO., LTD.		CHECKED : HY. KISHI 09.09.30		PART NO. JR25WP-24P(71)			
		DESIGNED : TH. KAMEYA 09.09.30		CODE NO. CL114-2011-9-71			
		DRAWN : YS. SAKODA 09.09.26				1/1	