


M-3232 8



NOTES: (UNLESS OTHERWISE SPECIFIED)

1) DIMENSIONS ARE: INCHES  
[ MM ]

2) TWO PLACE DECIMAL DIMENSIONS ARE ±.016 [ ±.4 ]

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
BODY	VALOX PBT/PET	
INSULATOR	.051 LAMINATED PHENOLIC	
STRAP	.040 C.R.S.	ZINC PLATE
CONTACT SPRINGS	.031 BRONZE	
GROUND SPRING	.031 BRONZE	
#8-32 BINDING SCREWS	BRASS	
#8-32 HEX HD. BIND. SCR.	BRASS	GREEN
RIVET	BRASS	

SYM	REVISIONS	APP	DATE
8	BODY MATERIAL "VALOX PBT/PET" WAS "UREA OR PHENOLIC" PER DCN 17476 WYA	EJM	3/29/11
7	REVISED BODY GEOMETRY TO AGREE WITH NEW PART DESIGN; BODY MATERIAL WAS UREA PER DCN 18957 RCM	DJP	9/17/10
6	REDRAWN ON CAD WITH CHANGES ON UPDATED FORMAT. "B" SIZE DWG. WAS "A" SIZE. ADDED NOTES 1 & 2. DECIMAL DIMENSIONS WERE FRACTIONAL; ADDED METRIC DIM.'S. LIST OF PARTS WERE CALL-OUTS. BODY MATERIAL "UREA" WAS "MOLDED PHENOLIC". REMOVED "DIMENSION SHEET FOR CAT. 5258" FROM DWG. TITLE ADDED "HBL5258" TO "DIMENSION SHEET FOR CAT. NO.". DWG. SCALE "NONE" WAS "FULL". "2X #8-32UNS-2B THREAD" WAS "#8-32 TAP" SUPERSEDES DWG. DATED 12/13/96 PER DCN # 12582 JMN	TJV	9/12/06

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE  
SINGLE RECEPTACLE-PANEL MOUNT

TOLERANCES UNLESS OTHERWISE SPECIFIED	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED BRIDGEPORT, CT	
FRACTIONS $\pm 1/64$	DR. BY CM	APP. BY TJV
DECIMALS $\pm .005$	TR. BY JMN	SCALE NONE
ANGLES $\pm 2'$	CHK'D BY TJV	DATE 9/12/06

DIMENSION SHEET FOR CAT. NO. HBL5258

REPAIRABLE

NON-REPAIRABLE

B

M-3232

8