


DRAWING NUMBER

NOTES:
UNLESS OTHERWISE SPECIFIED, ALL SPECIFICATIONS REFERENCED SHALL BE OF THE LATEST REVISION.


- 1) INTERPRET DRAWING PER IPC-2222, INTERPRET DIMENSIONS PER ASME Y14.5, WORKMANSHIP TO COMPLY WITH IPC-6012 AND INSPECTED PER IPC-A-600
- 2) MATERIAL:
STANDARD FR4
MATERIAL SHALL HAVE A FLAMMABILITY RATING OF 94V-0 OR BETTER. LAYER STACKUP AND COPPER THICKNESS AS SHOWN IN DETAIL A-A.
- 3) FINISH:
a) LPTSM - LIQUID PHOTO IMAGEABLE SOLDER MASK PER IPC-SM-840
b) SMDSC - SOLDER MASK OVER BARE COPPER
c) ENIG
- 4) TEST REQUIREMENTS:
a) ALL BOARDS SHALL BE 100% ELECTRICALLY TESTED AS DEFINED BY IPC-ET-662.
- 6) ALL PLATED HOLES SHALL HAVE A MINIMUM OF 0.02mm PLATING IN THE BAREL OF THE HOLE.
- 7) REMOVE ALL BURRS AND SHARP EDGES.
- 8) ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY. BOARD OUTLINES AND DRILL HOLE LOCATIONS SHOULD BE FABRICATED ACCORDING TO THE GERBER DATA PROVIDED, DIMENSIONS IN BOXES ARE CRITICAL DIMENSIONS

NO.	REVISION RECORD	ISS NUMBER	DATE	DRWNR
1	REV 1		18-07-18	CT




Drill Schedule - thru

Hole Symbol	Hole Size	Count	Plated	Tolerance
Q	1.050	128	YES	+/- .075
III	2.000	4	NO	+/- .080



CARD EDGE CONNECTOR BEVEL



THIS DOCUMENT IS CONFIDENTIAL INFORMATION
UNLESS OTHERWISE INDICATED OTHERWISE.
ANY DISCLOSURE OF THIS INFORMATION TO ANY
THIRD PARTY WITHOUT THE EXPRESS WRITTEN
CONSENT OF THE COMPANY IS STRICTLY
PROHIBITED. THE COMPANY SHALL NOT BE
RESPONSIBLE FOR ANY DAMAGES, INCLUDING
CONSEQUENTIAL DAMAGES, ARISING FROM THE
USE OF THIS DOCUMENT. THE COMPANY SHALL
NOT BE RESPONSIBLE FOR ANY DAMAGES, INCLUDING
CONSEQUENTIAL DAMAGES, ARISING FROM THE
USE OF THIS DOCUMENT. THE COMPANY SHALL
NOT BE RESPONSIBLE FOR ANY DAMAGES, INCLUDING
CONSEQUENTIAL DAMAGES, ARISING FROM THE
USE OF THIS DOCUMENT.

TITLE			
FABRICATION DRAWING, IOT BREAKOUT			
SIZE	UNITS	DWG NO	REV
A1	MM	1401148	1
SCALE			SHEET 1 of 1