









RECOMMENDED PATTERN



CODE NO.	PART NO.	CONTACT	A	B
CL543-0533-1-24	DF11-4DP-2DS(24)	4	6.0	2.0
CL543-0534-4-24	DF11-6DP-2DS(24)	6	8.0	4.0
CL543-0535-7-24	DF11-8DP-2DS(24)	8	10.0	6.0
CL543-0536-0-24	DF11-10DP-2DS(24)	10	12.0	8.0
CL543-0537-2-24	DF11-12DP-2DS(24)	12	14.0	10.0
CL543-0538-5-24	DF11-14DP-2DS(24)	14	16.0	12.0
CL543-0539-8-24	DF11-16DP-2DS(24)	16	18.0	14.0
CL543-0540-7-24	DF11-18DP-2DS(24)	18	20.0	16.0
CL543-0541-0-24	DF11-20DP-2DS(24)	20	22.0	18.0
CL543-0542-2-24	DF11-22DP-2DS(24)	22	24.0	20.0
CL543-0543-5-24	DF11-24DP-2DS(24)	24	26.0	22.0
CL543-0544-8-24	DF11-26DP-2DS(24)	26	28.0	24.0
CL543-0545-0-24	DF11-28DP-2DS(24)	28	30.0	26.0
CL543-0546-3-24	DF11-30DP-2DS(24)	30	32.0	28.0
CL543-0547-6-24	DF11-32DP-2DS(24)	32	34.0	30.0

2	BRASS	SURFACE: TIN PLATED UNDER PLATING: NI/CXCL PLATED 0.5μm min	1μm min	5	ELASTOMER	STOPPER, GREEN
1	POLYAMIDE	BLACK, UL94V-0		4	PS	ELECTROSTATIC PROTECTION, CLEAR
NO.	MATERIAL	FINISH, REMARKS		3	BRASS	SURFACE: TIN PLATED UNDER PLATING: NI/CXCL PLATED 0.5μm min
				NO.	MATERIAL	FINISH, REMARKS

REMARKS		DRAWN		DESIGNED	CHECKED	APPROVED	RELEASED
		A. Miura		05.10.24		05.10.27	
CODE NO. (OLD)		DRAWING NO.		PART NO.			
		EDC3-084779-02		DF11-*DP-2DS(24)			
SCALE 5 : 1		UNITS mm		CODE NO.		CL543-	
HRS		HIROSE ELECTRIC CO., LTD.		1		2	



Technical drawing of a mechanical part showing a cross-section. The part has a complex internal structure with a central cavity. Dimensions are given in millimeters: a vertical dimension of 4.6 ± 0.3 mm on the left, a horizontal dimension of 12.4 ± 0.5 mm at the bottom, and a vertical dimension of 11.4 ± 0.5 mm on the right. A label "PRINTED SURFACE" with an arrow points to the bottom edge of the part.

TO				
----	--	--	--	--

TO				
----	--	--	--	--