


Aug.1.2016 Copyright 2016 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
2	DIS-C-000490	T.H.E.K		07.01.31					



- NOTES
- 1 TOTAL LENGTH BECOMES 28.8±1 WHEN 6 IS SCREWED INTO 1 COMPLETELY.
  - 2 THE RECOMMENDED CLUMP TORQUE OF REF. NO. 6 TO BE 0.5N·m.  
LOCTITE 271, LOCPRIMER 7649, HENKEL JAPAN IS RECOMMENDED TO PREVENT REF. NO. 6 FROM LOOSENING.  
SPACER FOR ASSEMBLY IS AVAILABLE HR30-6P-T02.
  - 3 TABLE FOR ASSEMBLY AND SOLDERING IS AVAILABLE HR30-6R-6P-T01.
  - 4 SURFACE PLATING: GOLD PLATING 0.2μm min.  
UNDER PLATING: NICKEL PLATING 2μm min.
  - 5 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER,  
DEPENDING ON THE CABLE STRUCTURE.  
PLEASE CONFIRM BEFORE THE USE.

3	PPS	(BLACK)	UL94V-0	6	PBT	(BLACK)	UL94V-0
2	BRASS	4		5	CR	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH	REMARKS	NO.	MATERIAL	FINISH	REMARKS

CODE NO. (OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	M.HANYU	H.NAGANO	E.KUNII	M.SATO	
	'05. 8. 8	'05. 8. 8	'05. 8. 10	'05. 8. 10	

SCALE 5 : 1	DRAWING NO. EDC3-112103-71	PART NO. HR30-6J-6P(71)
UNITS mm	HRS HIROSE ELECTRIC CO., LTD	CODE NO. CL130-2009-6-71

TO
R