


Aug.1.2016 Copyright 2016 HIROSE ELECTRIC CO., LTD. All Rights Reserved.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
1	DIS-C-000490	T.H.E.k		07.01.31					




- NOTES
- 1 TOTAL LENGTH BECOMES 37.3±1 WHEN 6 IS SCREWED INTO 1 COMPLETELY.
 - 2 APPLICABLE CRIMPING CONTACT:HR30-PC-211
(APPLICABLE WIRE:26-30 AWG WIRE JACKET DIAMETER:φ1 MAX)
APPLICABLE CONTACT WITHDRAWAL HP30-TP
 - 3 THE RECOMMENDED CLUMP TORQUE OF REF. NO.6 TO BE 0.5N·m.
SPACER FOR ASSEMBLY IS AVAILABLE HR30-8P-T02.
STAND FOR ASSEMBLY IS AVAILABLE HR30-7J-12PC-T01.
 - 4 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE.
PLEASE CONFIRM BEFORE THE USE.

3	PBT	(BLACK)	UL94V-0	6	PPS	(BLACK)	UL94V-0
2	PPS	(BLACK)	UL94V-0	5	SYNTHETIC RUBBER	(BLACK)	
1	PPS	(BLACK)	UL94V-0	4	POLYACETAL	(NATURAL)	
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS	

CODE NO.(OLD)	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
	E.KUNII	E.KUNII		M.SATO	
	'05.10.14	'05.10.14		'05.10.17	

SCALE 5 : 1	DRAWING NO. EDC3-112268-71	PART NO. HR30-7J-12PC(71)
UNITS mm	HRS HIROSE ELECTRIC CO., LTD	CODE NO. CL130-2017-4-71

LIFE SIZE(1 : 1)



TO
R

F

F