



REVISIONS			
SN	EDN	DESCRIPTION	DATE
1			11/05/08

D-SUB TECHNICAL DATA

- SHELL : Steel 2.5um(100u") min tin over 1.25um(50u") min nickel
- BODY : Glass filled thermoplastic.
- CONTACTS : Flame retardant to UL94 V-0 Color Black
- Signal contacts:0.4um(15u") min gold over 1.25um(50") min nickel
- ELECTRICAL : Voltage rating 300 V RMS at 50 Hz
- Current rating 7.5A
- Withstanding Voltage >1000 V RMS at 50 Hz for one minute
- Insulation resistance >5000 M Ohms
- Contact resistance 20 mOhms max.
- CLIMATIC : Temperature range -55 °C up to 155°C
- Damp heat 56 days(40 °C-95% HR)
- MARKING : Amphenol...(Series No.)
- Commercial reference
- Manufacturing date



Customer drawing



PRODUCT CODE

L 77TW B 17W2 S

L: RoHS Compliance

77TW: tin plated shell

Shell Size :B

Contact type:
S:Female
P: Male

Configuration: 17W2

DIMENSION SPECIFIED				APPROVAL		DATE	
TOLERANCES				DRAWN		CHECKED	
U.S.				10/24/07		10/24/07	
METRIC				10/24/07		10/24/07	
X	±	0.50					
XX	±	0.30					
XXX	±	0.20					
ANGLES	±	S					
DIMENSIONS				DRAWING FILE :		TITLE	
REMOVE SHARP EDGES				ANGLE OF PROJECTION		Hybrid connector, TW series	
TOLERANCE				SCALE		SHEET 1 OF 1	
NONE				NONE		SHEET 1 OF 1	