




This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be distributed, reproduced or used, in whole or in part, without the prior written consent of Amphenol Corporation. Amphenol Corporation assumes no responsibility for the use of this document without its prior consent. All rights are reserved. No part of this document is to be reproduced or to use any information in this document.



Recommended PCB Layout



Dimensions	A	B	C	D	E
Positions					
9	30.81	24.99	16.92	16.33	11.08
15	39.14	33.32	25.50	24.66	19.39
25	53.04	47.04	38.96	38.38	33.24
37	69.32	63.50	55.42	54.84	49.86

REVISONS			
SN	EDN	DESCRIPTION	DATE
A			02/03/07

D-SUB TECHNICAL DATA

Product Specification

Material

Insulator :Glass-Filled Thermoplastic PBT,UL94V-0 rated

Contact :Brass

Shell :Steel, 100u" Tin Over 50u" min Nickel.

Boardlock :Brass, 100u" min Nickel Plated.

Screwlock :Brass, 100u" min Nickel Plated.

Electrical

Contact Resistance :20 milliohms

Max at 3 AMP DC.


Insulation Resistance :1000 megohms at 500 VDC

Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute

Current Rating :1 AMP

Voltage Rating :250 VAC/rms 60Hz

PRODUCT CODE



DIMENSIONS SPECIFIED			
TOLERANCES	U.S.	METRIC	APPROVAL
.X +/-.XX +/-.XXX +/-	0.50 0.30 0.20	CHECKED CHECKED	DATE LEON YU02/03/07 02/03/07
ANGLES +/-	2°		
FOR MATERIALS AND FINISHES			
SEE DRAWING			
REMOVE SHARP EDGES			
DRAWING FILE :			
DIMENSIONS	ANGLE OF PROJECTION		
THIRD ANGLE			
MM			
TITLE			
Straight PCB Termination one Metal Shell Connectors			
SIZE	DRAWING NO.		REV.
A4	C	L7TTS E H 09 S O L 2 R M 8	A
SCALE	NONE		SHEET 1 OF 1